


0.76µm Au	NO	ALL	200	1 - 2 3 3 6 5 6 8 - 1	
0.76µm Au	YES	ALL	200	1 - 2 3 3 6 5 6 8 - 3	
0.76µm Au	YES	ALL	200	1 - 2 3 3 6 5 6 8 - 0	
0.76µm Au			200	2336568-9	
0.38µm Au	NO	ALL	100	2336568-8	
FLASH Au/Pd Ni			50	2336568-7	
0.76µm Au			200	2336568-6	
0.38µm Au	YES	ENDS	100	2336568-5	
FLASH Au/Pd Ni			50	2336568-4	
0.76µm Au			200	2336568-3	
0.38µm Au	YES	ALL	100	2336568-2	
FLASH Au/Pd Ni			50	2336568-1	
PLATING	PICK AND PLACE TAPE	HOLD Downs	MATING CYCLES	PART NUMBER	А
CONTROLLED DOCUMENT. TARUN M CHK DAVID Z	08FEB2022 HANG		TE T	E Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 APVD D Z PRODUCT SPE 1 DLC ± 0.1 3 PLC ± 0.1 APVL ± 0.1 APVL ± 0.1 APVL ± 0.1 1 08-1. APVL ± 0.1 APVL ± 0.1 1 108-1. APVL ± 0.1 APVL ± 0.1 1 108-1. APVL ± 0.1 APVL ± 0.1 APVL ± 0.1 1 08-1. APVL ± 0.1 APVL	1 6 30021 - SPEC SIZE	8 POSITON	I, SILVER	RIGHT ANGLE, 2.0	
CUSTOMER	DRAWING		SCALE 8:1	SHEET OF REVD3	


		REVISIONS			
Ρ	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECN-22-153747	13MAY2022	ТΧ	DZ
	D 1	ADDED 3 COREOUT FEATURES	23NOV2022	ТМ	DZ
	D 2	REVISED PER ECN-24-266777	20MAY2024	ΤR	JM
	D 3	REVISED PER ECN-25-313218	25MAR2025	A D	JM

	8		7	6
THIS DRAWING IS UNPUBLIS		FOR PUBLICATION RIGHTS RESERVED.	20	
			DETAIL SCALE	HEAT STA

5	4	3

TAKING FOR RT NUMBERS





THIS	DRAWING	ΙS	А	С	0
	DIMENSIONS	:			
	mm				0
	ф-			7	
	() t	_		t	1 2 3 4
MATERIA	1				A
MATERIA	L				F

Р	LTR	DESCRIPTION	DATE	DWN	APVC
	-	SEE SHEET 1	-	-	-


REVISIONS

1


SAC	ONTROLLED DOCUMENT.	DWN 08FEB2022 TARUN MARRI снк 08FEB2022 DAVID 7HANG	-	-		E	E Conn	ec†	ivity	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 08FEB2022 DAVID ZHANG	name R	ECEPTA	CLE AS	SEMBLY,	RIG	НT	ANGL	_E,
	0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1	PRODUCT SPEC 108-130021 APPLICATION SPEC				SILVER				,
	4 PLC ±0.1 ANGLES ±2°	114-130008	SIZE	CAGE CODE	DRAWING NO				RES	TRICTED TO
	FINISH	WE IGHT _	A 1	-	\mathbb{C} -23	36568				-
		CUSTOMER DRAWING				scale 8:1	SHEET	2	of 5	Rev D 3

D

В




DRAWING	ΙS	А	(
DIMENSIONS	:					
mm						
L						
	DIMENSIONS mm	DIMENSIONS: mm	mm			



MATERIAL





С	ONTROLLED DOCUMENT.	DWN 08FEB2022 TARUN MARRI снк 08FEB2022 DAVID ZHANG			E <i>T</i>	TE Co	onnectiv	/ity
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 08FEB2022 DAVID ZHANG PRODUCT SPEC				SEMBLY, R		ANGLE,
]	0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1	108-130021 APPLICATION SPEC	1	68 POS	ITON,	SILVER 2.	0	
	4 PLC ±0.1 ANGLES ±2°	114-130008	SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
	FINISH	WEIGHT _	A 1	-	\mathbb{C} - 233	36568		-
		CUSTOMER DRAWING				scale 10:1 she	ет 4	5 ^{rev} D3

D


В

8		7	6
THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20	
C COPYRIGHT 20 BY -	ALL RIGHTS RESERVED.		

CONNECTOR CONTACT IDENTIFICATION Δ

	-	-
CONTACT NUMBER	SIDE A	SIDE B
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
4 1	GROUND	GROUND
42	GROUND	GROUND
43	GROUND	GROUND
44	SIGNAL	SIGNAL
4 5	SIGNAL	SIGNAL
46	GROUND	GROUND
47	SIGNAL	SIGNAL
48	SIGNAL	SIGNAL
49	GROUND	GROUND
50	SIGNAL	SIGNAL
5 1	SIGNAL	SIGNAL
52	GROUND	GROUND
53	SIGNAL	SIGNAL
54	SIGNAL	SIGNAL
55	GROUND	GROUND
56	SIGNAL	SIGNAL
57	SIGNAL	SIGNAL
58	GROUND	GROUND
59	SIGNAL	SIGNAL
60	SIGNAL	SIGNAL
6 1	GROUND	GROUND
6 2	SIGNAL	SIGNAL
63	SIGNAL	SIGNAL
64	GROUND	GROUND
6 5	SIGNAL	SIGNAL
6 6	SIGNAL	SIGNAL
67	GROUND	GROUND
68	SIGNAL	SIGNAL
6 9	SIGNAL	SIGNAL
70	GROUND	GROUND

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
1 0	GROUND	GROUND
1 1	SIGNAL	SIGNAL
1 2	SIGNAL	SIGNAL
1 3	GROUND	GROUND
1 4	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
1 6	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
1 9	GROUND	GROUND
20	SIGNAL	SIGNAL
2 1	SIGNAL	SIGNAL
2 2	GROUND	GROUND
2 3	SIGNAL	SIGNAL
2 4	SIGNAL	SIGNAL
2 5	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND
2 9	GROUND	GROUND
30	SIGNAL	SIGNAL
31	SIGNAL	SIGNAL
32	GROUND	GROUND
33	SIGNAL	SIGNAL
3 4	SIGNAL	SIGNAL
35	GROUND	GROUND



DETAIL H SCALE 4:1


4805 (3/13)

HARD TRAY PACKAGING-1. DIMENSIONS: TRAY: L= (330), W= (136), H= (14.5) 2. QUANITY: 32 pieces per tray.

5

CONTACT NUMBER	SIDE OA	SIDE OB
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
1 0	GROUND	GROUND
1 1	SIGNAL	SIGNAL
1 2	SIGNAL	SIGNAL
1 3	GROUND	GROUND
1 4	GROUND	GROUND


4




3


DETAIL J SCALE 4:1

—see detail H



CHAMFERED CORNER-






\sim	
/	
L_	

DESCRIPTION	DATE	DWN	APVD
			AFVD
SEE SHEET 1	-	-	-

1





CONTROLLED DOCUMENT.		DWN 08FEB2022 TARUN MARRI снк 08FEB2022 DAVID ZHANG				E	TE Conn	ecti	vity	
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1	APVD 08FEB2022 DAVID ZHANG PRODUCT SPEC 108-130021 APPLICATION SPEC				SEMBLY SILVER		ΗT	ANG	LE,
	4 PLC ±0.1 ANGLES ±2° FINISH	114-130008 WEIGHT _	size A 1	CAGE CODE —	DRAWING NO				RE	STRICTED TO -
		CUSTOMER DRAWING				scale 8:1	SHEET	5	of 5	rev D 3