

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-19-002431	15FEB2019	BKW	GJ
	A2	REVISED PER ECO-19-013371	29AUG2019	BKW	GJ
	A3	REVISED PER ECR-20-100211	06AUG2020	JP	VS
	B	REVISED PER ECN-25-317844	10APR2025	MMK	JHW

D

D

C


C

B




B

A


A




- 1 MATERIAL MARK
2. RECOMMENDED WIRE RANGE:
AWG 22-26 COPPER STRANDED
3. INSULATION DIAMETER RANGE:
1.3~2.4mm
4. SUPPLIED CONTINUOUS ON A REEL



SECTION A-A



SECTION B-B



SECTION C-C

M1		BRASS	STANDARD TEMP. (105°C)		2329909-1
MATERIAL MARK 1		MATERIAL	TEMPERATURE RATING		PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASAVARAJA D A 27MAR2018	TE Connectivity		
		CHK S. FERNANDES 27MAR2018			
DIMENSIONS: mm		APVD C.YI 27MAR2018	NAME POWER VERSA-LOCK TAB TERMINAL UNSEALED 22-26 AWG		
		PRODUCT SPEC 108-143081	SIZE A2		RESTRICTED TO -
		APPLICATION SPEC 114-143082	CAGE CODE -		
MATERIAL -		WEIGHT -	DRAWING NO C-2329909		
SEE TABLE		PRE-PLATED Sn	CUSTOMER DRAWING		
			SCALE 10:1	SHEET 1 OF 1	REV B