



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16NOV2018	FL	PW
	A1	REVISED ECO-19-013318	29AUG2019	AG	PW



CODE I AS SHOWN
OTHER CODE REFER TO TABLE 1

WIRING SCHEDULE:

TE P/N	REV	LENGTH	TOL.	CUSTOMER P/N	CAVITY 1	CAVITY 2	FROM	TO
2330574-1	A	6400	±40	P00336808	WHITE	BLUE	C3R114B	C9R109
2330574-2	A	4640	±30	P00336809	ORANGE	GREY	C3R114B	C9R111
2330574-3	A	2480	±20	P00336810	PINK	BROWN	C3R114B	C3R122
2330574-4	A	5870	±40	P00336811	GREEN	BLUE	C3R114B	C3R120
2330574-5	A	3315	±30	P00336812	GREY	YELLOW	C3R114B	C3R171
2330574-6	A	4800	±30	P00336816	ORANGE	VIOLET	C3R114B	C3R172
2330574-7	A	1670	±20	P00336820	ORANGE	WHITE	C3R114B	C3R105
2330574-8	A	1650	±20	P00336821	YELLOW	VIOLET	C3R114B	C3R106
2330574-9	A	1570	±20	P00336822	GREY	VIOLET	C3R114A	C2R103A



NOTE:

- 1. 100% ELECTRICAL TEST: ACCORDING TO TEST SPECIFICATION 108-18857
- 2. CRIMPING ACCORDING TO 114-18972
- 3. S-TWIST LENGTH: 20±2
- 4. CPA SHOULD IN PRE-LOCKED POSITION
- 5. WIRE CRIMPING FORCE 50N min
- 6. PRINTER DETAIL AS BELOW





TABLE 1



"D" PART

--	--	--	--	--	--	--	--	--	mm	SEE TABLE	TWISTED WIRE, 2X0.35mm ² FLRY-A	7
1	1	1	1	1	1	1	1	1	PC	2282031-1	SQUIB CONN., FERRITE	6
1	1	1	1	1	1	1	1	1	PC	1564882-1	SOCKET CONTACT FOR 1MM DIA PIN, RIGHT	5
1	1	1	1	1	1	1	1	1	PC	1564881-1	SOCKET CONTACT FOR 1MM DIA PIN, LEFT	4
1	1	1	1	1	1	1	1	1	PC	2-1563975-2	SQUIB CONN., COVER	3
1	1	1	1	1	1	1	1	1	PC	1-1563976-1	SQUIB CONN., CPA	2
1	-	-	-	-	-	-	-	-	PC	2-1563974-2	2 POS, SQUIB HOUSING, CORDING II, GREEN	1
-	1	1	1	1	1	1	1	1	PC	2-1563974-1	2 POS, SQUIB HOUSING, CORDING I, BLACK	
-9	-8	-7	-6	-5	-4	-3	-2	-1	U/M	PART NO.	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F.LEE 16NOV2018	TE Connectivity	
DIMENSIONS: mm		CHK P.WU 24JAN18		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD P.WU 24JAN18	NAME	
MATERIAL		FINISH	SIZE A2	
			CAGE CODE 00779	
			DRAWING NO C-2330574	
			RESTRICTED TO -	
			RESTRICTED CUSTOMER	
			SCALE -	
			SHEET 1 of 1	
			REV A1	