










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18OCT18	B.Z	W.W
	A1	ECR-19-019964	23DEC19	B.Z	W.W
	A2	ECN-23-221302	11JUL23	M.X	F.P



- 1 HSD INTERFACE DESIGN ARE LEFT TO TE CONNECTIVITY
- 2 ALL DIMENSIONS IN BRACKETS () FOR INFORMATION ONLY
- 3 PACKAGING: TAPE AND REEL
- △4 MARKING OF 100% TEST PASSED
- △5 CENTER OF GRAVITY
- △6 AREA OF VACUUM GRIPPER

WEIGHT (g): 3.2
AS SHOWN CODING Z



SCALE 2:1

1								PICK-UP CAP	NYLON	BLACK	6
2								MOS PIN	CuSn4	TIN PLATING	5
1								SHIELDING BODY	Zn ALLOY	SOLDER SIDE: TIN PLATING. INTERFACE SIDE(OUTER CONTACT): TIN PLATING.	4
4								CONTACT PIN	CuSn4	SOLDER SIDE: TIN PLATING. INTERFACE SIDE: GOLD PLATING	3
1								CAVITY BLOCK	PA4T	BLACK	2
						1	Z	CODING COVER	PA6T/66	WATER BULE / 5021	1
						1	F			NUT BROWN / 8011	
				1			E			LEAF GREEN / 6002	
			1				D			CLARET VIOLET / 4004	
			1				C			SIGNAL BLUE / 5005	
	1						B			CREAM WHITE / 9001	
1							A			JET BLACK / 9005	
QUANTITY							CODE	DESCRIPTION	MATERIAL	FINISH COLOR, SIMILAR RAL	ITEM NO.
0-1	0-2	0-3	0-4	0-5	0-6	0-9	ASSY NO. X-2345180-Y				
A	B	C	D	E	F	Z	ASSY CODE				
1	1	1	1	1	1	1	REVISION				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ML-XU	11JUL2023	TE Connectivity	
DIMENSIONS:		CHK C.PAN	11JUL2023		
		APVD F.PAN	11JUL2023		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-101388		NAME 6 POS HSD 180DEG HEADER ASSY WITH PLASTIC CAP	
0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.5 3 PLC ±0.5 4 PLC ±0.5 ANGLES ±0.5 FINISH -		APPLICATION SPEC			
MATERIAL SEE TABLE		116-32195		SIZE A 1	
CUSTOMER DRAWING		WEIGHT -		CAGE CODE -	
		DRAWING NO C=2345180		RESTRICTED TO -	
		SCALE 5:1		SHEET 1 OF 1	
		REV A2			