





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-20-010202	09JUL2020	DCB	DH



- 1 "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 [50.8] LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-0
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING:
POWER CONTACTS - .000050 [0.00127] MIN Ni UNDER ALL
.000050 [0.00127] MIN Au ON CONTACT AREA
.000005 [0.00013] MIN Au AT PCB INTERFACE
- 4 CONNECTOR OUTLINE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7 PCB - .0453±.0010 [1.151±0.025] DRILLED HOLES PLATED WITH .0003 [0.008] MIN Sn OVER .001-.003 [0.03-0.08] Cu PLATING TO ACHIEVE A .040±.003 [1.02±0.08] HOLE.
- 8 SUGGESTED NON-PLATED CLEARANCE SLOTS FOR HIGH VOLTAGE APPLICATIONS. OPTIONAL HIGH VOLTAGE FIN COMPONENTS 2313444-1 SOLD SEPARATELY (6 PER CONNECTOR).



7P	2348888
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 18DEC2018	TE Connectivity TE	
DIMENSIONS: INCHES [mm]		CHK C.GINGRICH 18DEC2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.GINGRICH 18DEC2018	NAME VERTICAL RECEPTACLE, PRESS FIT MULTI-BEAM XLE VITA 62.2 6U J0	
0 PLC ±.005 1 PLC ±.005 2 PLC ±.005 3 PLC ±.005 4 PLC ±.005 ANGLES ±.020 FINISH #2		PRODUCT SPEC 108-163023 APPLICATION SPEC 114-13251		
MATERIAL - -		WEIGHT -	SIZE A100779	
RESTRICTED CUSTOMER		CAGE CODE 2348888		RESTRICTED TO
SCALE 4:1		SHEET 1 OF 2		REV A

