



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
 © COPYRIGHT 2006 ALL RIGHTS RESERVED.



LOC		DIST		REVISIONS		
P	LTR	DESCRIPTION	DATE	DWN	APVD	
A		INITIAL RELEASE	27MAY2019	F.Z	R.B	




40POS(X-KEY):1-1903128-0



RECOMMENDED PANEL LAYOUT
 (APPLICABLE PANEL THICKNESS : 0.8, 1.0, 1.6, 2.0)



1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.



AS SHOWN 40POS : 1-2350416-0

40	X	19	38.041.042.641.221.348.7850.142.939.31-2350416-0
POS	KEY	n	A B C D E F G H J PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER, ZHU 03-Jul-19	 TE Connectivity
DIMENSIONS: mm		CHK RICK, BIAN 03-Jul-19	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±3°		APVD RICK, BIAN 03-Jul-19	
0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-78268,78298 APPLICATION SPEC 114-5377 WEIGHT	
MATERIAL		RESTRICTED CUSTOMER	NAME DYNAMIC D1100D 2.0mm PITCH TAB HSG, PANEL MOUNT TYPE 40 POS SIZE CAGE CODE DRAWING NO RESTRICTED TO A200779 C-2350416
		SCALE 4:1	SHEET 1 OF 1 REV A