


6. RECOMMENDED STENCIL THICKNESS:0.14MM.



30u”Min	3.00mm	2356320-6
	2.20mm	2356320-5
	1.50mm	2356320-4
15u”Min	3.00mm	2356320-3
	2.20mm	2356320-2
	1.50mm	2356320-1
GOID PLATING	”DIM”A	TE P/N

1471-9 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

C

B

A



D

C



B

A


FEEDING DIRECTION



DETAIL A
SCALE 4:1



1. MATERIAL:
COVER TAPE: PET, COLOR: CLEAR
CARRIER TAPE: PET
REEL: PET
SHIPPING BOX; CORRUGATED FIBER
2. DIMENSION:
REEL: SEE DRAWING
BOX: 385X385X223mm
3. QUANTITY: SEE TABLE



2356320-X	350	4	1400
PART NO.	PCS/ REEL	REEL/ BOX	PCS/ BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 27AUG2019	 TE Connectivity	
		CHK DAVID ZHANG 07MAY2019		
		APVD DAVID ZHANG 07MAY2019	NAME	
		PRODUCT SPEC	SLIM SAS X8 74P, RECEPTACLE RIGHT ANGLE TYPE	
		APPLICATION SPEC	-	
		WEIGHT	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=2356320	RESTRICTED TO -
			SCALE 4:1	SHEET 2 OF 2
				REV B1

2356320