






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-25-328321	05MAY2025	TR	SKN



- 1 CAGE ASSEMBLY: STAINLESS STEEL
HEAT SINK: ALUMINUM/ANODIZED BLACK
HEAT SINK CLIP: STAINLESS STEEL
EMI SPRING: COPPER ALLOY/ NICKEL PLATED
- 2 REFERENCE APPLICATION SPECIFICATION 114-60025
FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING
THICKNESS. BOARD LAYOUT PER THIS PRINT.
- 3 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
- 4 DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
5. MATES WIHT QSFP-DD MSA COMPATIBLE TRANSCEIVER.
6. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 3.0 MIN



-	18.50	2342886-4	CAGE ASSY WITH HS	4
NET	23.00	2342886-3	CAGE ASSY WITH NET HS	3
SAN	16.00	2342886-2	CAGE ASSY WITH SAN HS	2
PCI	13.70	2342886-1	CAGE ASSY WITH PCI HS	1
HS SPECIFICATION	DIM A	PART NUMBER	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
TBD

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN 05MAY2025
CHK SEAN HAN
APVD SEAN HAN
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

05JUL2018
22AUG2018

CUSTOMER DRAWING

TE Connectivity


CAGE ASSEMBLY WITH HEAT SINK FOR GM QSFP-DD, 1X3

SIZE A2
CAGE CODE 00779
DRAWING NO C-2342886


RESTRICTED TO -

SCALE 5:1 SHEET 1 OF 6 REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





SCALE 3:1




DIM. A MAX.
(AFTER TRANSCEIVER
PLUGED)

2342886-4 AS SHOWN :
SAME AS -1 EXCEPT THE HEAT SINK AND NO REAR PINS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05MAY2025 STEPHEN HE	 TE Connectivity			
DIMENSIONS:		CHK 05JUL2018 SEAN HAN				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 22AUG2018 SEAN HAN	NAME CAGE ASSEMBLY WITH HEAT SINK FOR GM QSFP-DD, 1X3			
	0 PLC ±-	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
	1 PLC ±0.5	-	A200779C-2342886			
	2 PLC ±0.13	APPLICATION SPEC	SCALE 5:1 SHEET 2 OF 6 REV A1			
	3 PLC ±0.013	-				
MATERIAL	4 PLC ±0.0001	WEIGHT				
	ANGLES ±-	-				
TBD	FINISH	CUSTOMER DRAWING				
-	-					



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05MAY2025 STEPHEN HE	TE Connectivity		
DIMENSIONS:		CHK 05JUL2018 SEAN HAN			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 22AUG2018 SEAN HAN	NAME CAGE ASSEMBLY WITH HEAT SINK FOR GM QSFP-DD, 1X3		
	0 PLC ±-	PRODUCT SPEC -	SIZE	CAGE CODE	DRAWING NO
	1 PLC ±0.5	APPLICATION SPEC -	A2	00779	C-2342886
	2 PLC ±0.13	WEIGHT -	RESTRICTED TO -		
	3 PLC ±0.013	CUSTOMER DRAWING	SCALE 5:1	SHEET 4 OF 6	REV A1
	4 PLC ±0.0001				
	ANGLES ±-				
MATERIAL	FINISH -				
TBD	-				
-	-				

