

4805 (3/13)

- HOUSING AND PIN SPACER THERI
- BASED ON TELCORDIA GR-1217-COI APPLICATIONS IN CONTROLLED EN' COMPLIANT PIN AREA : 0.5um MI
- GROUND PLATED THRU HOLE REQUIR HOLE SIZE PRIOR TO PLATING = \$ IMMERSION TIN IF APPLICABLE =
- A SIGNAL PLATED THRU HOLE REQUIR HOLE SIZE PRIOR TO PLATING = 9 IMMERSION TIN IF APPLICABLE =
- SI VIA PLATED THRU HOLE REQUIR HOLE SIZE PRIOR TO PLATING = \$ IMMERSION TIN IF APPLICABLE =
- CONNECTOR MARKED WITH PART NUM

2					1					
				REVISIONS						
	Р	LTR		DESCRIPTION		DATE	DWN	APVD		
		А	RELEASED			I6DEC20I9	Y.K	Τ.Μ		
		ΑI	REVISED			24DEC2019	Y.K	Τ.Μ		
ALLOY										
MOPLASTIC, U		94	V-0, B	LACK						
OF TE PRODUCT SPECIFICATION 108-140186 RE FOR SYSTEM QUALITY LEVEL 111, VIRONMENTS (CENTRAL OFFICE). N MATTE TIN. EMENTS:										
\emptyset 0.450 \pm 0.025										
(0.00095)										
EMENTS:										
Ø0.368±0.025 (#79 DRILL)										
(0.00095)										
EMENTS:										
$ \emptyset$ 0.254 \pm 0.025)									
(0.00095)										
TOP I.00mm O	F	Τŀ	E PCB	ΤΗΙΟΚΝΕ	ISS FRC) M TH	ΗE			
TOP I.25mm O	F	ΤH	E PCB	ΤΗΙΟΚΝΕ	ISS FRC) M TH	ΗE			
BER, DATE CODE, AND "92 OHM" IN										
ULN, VAIL CUVL, ANV JZ UNMI IN										
TABLISHED BY	(CUS	STOMER							
TER										

Ν	G
G	

				2356426-1
				PART NO
	ONTROLLED DOCUMENT.	DWN Y.KODAIRA Снк I3MAY2019 M.IWASAKI	€ TE	TE Connectivity
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3	APVD I 3MAY2019 T.MATSUDAIRA PRODUCT SPEC 108-140186 APPLICATION SPEC	RIGHT ANGLE RECEF 4 PAIR 4 COLUMN, PAIR-IN-ROW, STF	
	4 PLC ±0.3 ANGLES ±3° FINISH	II4-32029 Weight _ CUSTOMER DRAWING	SIZE CAGE CODE DRAWING NO A 1 0079 C=C-2356 SCALE	426 - 426 - 6:1 SHEET 1 OF 2 REVAL









