

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASE	03JUL2019	SZ	SZ
	A1	ECO-20-010950	05AUG2020	SZ	SZ
	A3	ECO-21-002794	01MAR2021	RY	SH

NOTES, UNLESS OTHERWISE SPECIFIED

1. MATERIAL:
HOUSING - THERMOPLASTIC, GLASS PREINFORCED, COLOR, BLACK, UL 94V-0
CONTACTS - COPPER ALLOY.
2. FINISH:
MATING AREA - 30u" GOLD OVERALL NICKEL.
SOLDER TAIL - MATTE TIN OVERALL NICKEL.
3. MARK P/N AND DATA CODE IN APPROX. AREA AS SHOWN.
4. NO TOOLING









TABLE 1


4	2.90 ^{+0.35} _{-0.15}	8.35±0.25	2343428-2
	3.10 ^{+0.35} _{-0.15}	8.15±0.25	2343428-1
	DIMENSION B	DIMENSION A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD YU 01MAR2021	TE Connectivity	
DIMENSIONS:		CHK -		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD SEAN HAN 01MAR2021	NAME HDCE PLUS, RIGHT ANGLE 2X6 POWER, 2X7 SIGNAL	
0 PLC ±0.50	1 PLC ±0.25	PRODUCT SPEC		
2 PLC ±0.25	3 PLC ±0.25	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO. RESTRICTED TO	
4 PLC ±0.25	ANGLES ±0.25	WEIGHT		
MATERIAL	FINISH	CUSTOMER DRAWING	A100779C=2343428	
			SCALE 5:1	SHEET 1 OF 2 REV A3

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



A1 ALTERNATIVE CHAMFER
FOR MATING BOARD EDGE



NOTES FOR MOUNTING BOARD, UNLESS OTHERWISE SPECIFIED:
1. PLATED THROUGH HOLE,
FINISHED HOLE SIZE: 1.15mm.
DRILL HOLE SIZE: 1.25±0.025mm.
2. COPPER PLATING THICKNESS: 0.025~0.05mm.
3. SURFACE FINISH: OSP OR IMMERSION TIN PLATING
IS RECOMMENDED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: RICHARD YU CHK: -	01MAR2021	 TE Connectivity		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: SEAN HAN PRODUCT SPEC	01MAR2021	NAME: HDCE PLUS, RIGHT ANGLE 2X6 POWER, 2X7 SIGNAL
mm				APPLICATION SPEC		SIZE: A1
MATERIAL		FINISH		WEIGHT		CAGE CODE: 2343428
				CUSTOMER DRAWING		RESTRICTED TO
						SCALE: 5:1
						SHEET 2 OF 2
						REV A3