





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO 20-004476	4-2-20	CT	FB

D




CIRCUIT	CABLE SIZE
A1, A2	.086
B1, B2	.086
C1, C2	.086
D1, D3	.086
D2	.047

C



B




A

- 1 MATERIAL:
INNER AND OUTER SHELL AND BACKPLATE - ALUMINUM ALLOY
GUIDE PIN - 300 SERIES STAINLESS STEEL
SCREWS - 300 SERIES STAINLESS STEEL
- 2 FINISH:
INNER AND OUTER SHELL AND BACKPLATE - CLEAR CHROMATE CONVERSION COATING
SCREWS AND GUIDE PIN - PASSIVATED
3. SHIPPED IN KIT FORM. BACKPLATE SCREWS TO BE ASSEMBLED TO BACKPLATE.
- 4 CIRCUIT IDENTIFICATION MARKING
5. DESIGNED TO BE USED WITH NanoRF CONTACTS 2302345-1 (.047 CABLE)
AND 2332772-1 (.086 CABLE).

2357971-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. MILLER CHK K. DOWHOWER APVD	08JUL2019 16AUG2019 -
DIMENSIONS: INCHES/mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-163006 APPLICATION SPEC 408-163016
MATERIAL		FINISH	WEIGHT
1		2	CUSTOMER DRAWING
NAME NanoRF MODULE, BACKPLANE 8 POSITION .086 CABLE PLUS 1 POSITION .047 CABLE, VITA 67.3		SIZE A1	CAGE CODE 00779
DRAWING NO. 2357971		RESTRICTED TO	REV A
SCALE 5:1		SHEET 1	OF 2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



J1B	1.541[39.15]
J2A	2.097[53.27]
J2B	2.653[67.39]
J3A	3.785[96.14]
J3B	4.341[110.26]
J4A	4.919[124.94]
J4B	5.475[139.06]
J5A	6.053[153.74]
J5B	6.609[167.86]
J6A	7.187[182.54]
J6B	7.743[196.66]
POSITION	DIM "X"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. MILLER CHK K. DOWHOWER APVD	08JUL2019 16AUG2019 -
DIMENSIONS: INCHES/mm		PRODUCT SPEC 108-163006	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±" 1 PLC ±" 2 PLC ±" 3 PLC ±.005[0.13] 4 PLC ±" ANGLES ±" FINISH		APPLICATION SPEC 408-163016	
MATERIAL		WEIGHT	
CUSTOMER DRAWING		SCALE 5:1 SHEET 2 OF 2 REV A	

TE Connectivity

NanoRF MODULE, BACKPLANE
8 POSITION .086 CABLE PLUS
1 POSITION .047 CABLE, VITA 67.3

SIZE CAGE CODE DRAWING NO
A100779C=2357971

RESTRICTED TO