






1. MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC,
UL94-V0; COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.1 μ m GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 μ m BRIGHT TIN OVER NICKEL UNDER PLATING.


2. PACKAGING: TAPE AND REEL (WITH PICK AND PLACE CAP).

3. TOLERANCE NOT CUMULATIVE.

4. CUTTING BURR MAX. 0.25 mm



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW / PIN-IN-PASTE

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09APR2019 RAGHAVENDRA K CHK 14AUG2019 KARTHIK.JK APVD 16AUG2019 PRASHANTH PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259 WEIGHT -		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±°		NAME AMPMODU 2mm BREAKAWAY HEADER, SINGLE ROW, VERTICAL, 0.1 Au, T/R PICK AND PLACE CAP	
MATERIAL SEE NOTES -		FINISH SEE NOTES -		SIZE A2	CAGE CODE 00779
				DRAWING NO C=2355122	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1
				REV	B

48.0	50.0	25	2-2355122-5
46.0	48.0	24	2-2355122-4
44.0	46.0	23	2-2355122-3
42.0	44.0	22	2-2355122-2
40.0	42.0	21	2-2355122-1
38.0	40.0	20	2-2355122-0
36.0	38.0	19	1-2355122-9
34.0	36.0	18	1-2355122-8
32.0	34.0	17	1-2355122-7
30.0	32.0	16	1-2355122-6
28.0	30.0	15	1-2355122-5
26.0	28.0	14	1-2355122-4
24.0	26.0	13	1-2355122-3
22.0	24.0	12	1-2355122-2
20.0	22.0	11	1-2355122-1
18.0	20.0	10	1-2355122-0
16.0	18.0	9	2355122-9
14.0	16.0	8	2355122-8
12.0	14.0	7	2355122-7
10.0	12.0	6	2355122-6
8.0	10.0	5	2355122-5
6.0	8.0	4	2355122-4
4.0	6.0	3	2355122-3
2.0	4.0	2	2355122-2
DIM "F"	DIM "E"	POS	TE PN