




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11MAY2022	LL	DZ

D






W/ PICK AND PLACE TAPE
SCALE 4:1



W/ CAP
SCALE 4:1

C




- NOTES
1. MATERIALS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS STEEL
CONTACT: COPPER ALLOY.
PICK AND PLACE TAPE: POLYIMIDE FILM.
2. FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100U" MIN.
UNDER PLATING: NICKEL PLATING 50u" min OVER ALL.
SHELL: UNDER PLATING: NICKEL PLATING 50u" min OVERALL.
3. HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-72

4. TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.
5. PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.

600	20	200	W/CAP	30u" GOLD	4.20MM	I-2360189-8	
					3.00MM	I-2360189-7	
					2.20MM	I-2360189-6	
				15u" GOLD	1.50MM	I-2360189-5	
					4.20MM	I-2360189-4	
			W/PICK AND PLACE TAPE	30u" GOLD	3.00MM	I-2360189-3	
					2.20MM	I-2360189-2	
					1.50MM	I-2360189-1	
				15u" GOLD	4.20MM	2360189-8	
					3.00MM	2360189-7	
Q'TY/CARTON		POCKET TAPE PITCH	Q'TY/REEL	CAP OPTION	CONTACT FINISH	DIM A	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN: LEO LI 05-AUG-2019	TE Connectivity MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD. 124P, SMT TYPE, 920HM			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK: DAVID ZHANG 05-AUG-2019				
mm		0 PLC ±0.30	APVD: DAVID ZHANG 05-AUG-2019				
		1 PLC ±0.20	PRODUCT SPEC				
		2 PLC ±0.20	108-60133				
		3 PLC ±0.10	APPLICATION SPEC				
		4 PLC ±"	114-60030				
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-	-	A1	00779	C=2360189	-
-		-	CUSTOMER DRAWING	SCALE 5:1		SHEET 1 OF 5	REV A1

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT
(GENERAL TOLERANCES: ±0.05)

SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.30

2 PLC ±0.20

3 PLC ±0.10

4 PLC ±

ANGLES ±2°

FINISH

WEIGHT

-

-

DWN: LEO LI 05-AUG-2019

CHK: DAVID ZHANG 05-AUG-2019

APVD: DAVID ZHANG 05-AUG-2019

PRODUCT SPEC 108-60133

APPLICATION SPEC 114-60030

CUSTOMER DRAWING

NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD. 124P, SMT TYPE, 920HM

SIZE: A

CAGE CODE: 00779

DRAWING NO: 2360189


RESTRICTED TO: -

SCALE: 5:1




SHEET: 2 OF 5

REV: A1

RECOMMENDED AIC MATING CARD DIMENSIONS



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 05-AUG-2019	TE Connectivity	
DIMENSIONS:		CHK: DAVID ZHANG 05-AUG-2019		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: DAVID ZHANG 05-AUG-2019	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 920HM	
	0 PLC ±°	PRODUCT SPEC	SIZE: A	
	1 PLC ±0.30	108-60133	CAGE CODE: 00779	
	2 PLC ±0.20	APPLICATION SPEC	DRAWING NO: C=2360189	
	3 PLC ±0.10	114-60030	RESTRICTED TO: -	
	4 PLC ±°	WEIGHT: -	SCALE: 5:1	
MATERIAL: -	FINISH: -	CUSTOMER DRAWING	SHEET 5 OF 5	
			REV A1	