

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11MAY2022	LL	DZ
	B	PER ECR-22-158369	21NOV2022	WZ	DZ
	B2	ADD W/O PICK UP PN	30OCT2023	FD	DZ
	B3	CLARIFICATION PCB DIMENISON	13NOV2023	FD	MP

D

C

B






A

D


C


B

A



- 1 MATERIALS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS STEEL
CONTACT: COPPER ALLOY
PICK AND PLACE TAPE: POLYIMIDE FILM.
- 2 FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100u".
SHELL: UNDERPLATING: NICKEL PLATING 50u" MIN OVERALL.
- 3 HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-72.
- 4 TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.
- 5 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.



800	20	200	W/O PICK UP	30u" GOLD	1.50	2-2359366-5	
				15u" GOLD	1.50	2-2359366-1	
			W/CAP	30u" GOLD	1.20	1-2359366-9	
					4.20	1-2359366-8	
					3.00	1-2359366-7	
					2.20	1-2359366-6	
				15u" GOLD	1.50	1-2359366-5	
					4.20	1-2359366-4	
					3.00	1-2359366-3	
					2.20	1-2359366-2	
			W/PICK AND PLACE TAPE	30u" GOLD	1.50	1-2359366-1	
					1.20	2359366-9	
					4.20	2359366-8	
					3.00	2359366-7	
				15u" GOLD	2.20	2359366-6	
1.50	2359366-5						
4.20	2359366-4						
3.00	2359366-3						
2.20	2359366-2						
1.50	2359366-1						
Q'TY /CARTON (PCS)	POKET TAPE PITCH(MM)	Q'TY /REEL (PCS)	CAP OPTION	 CONTACT FINISH	DIM A	PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN MIKE 04JULY2019	 TE Connectivity			
			CHK MICHAEL 04JULY2019				
			APVD MICHAEL 04JULY2019				
			NAME				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	MINI COOL EDGE IO INTEGRATED CONN. 0.6 PITCH, VERTICAL STANDARD 8X, SMT TYPE, 92OHM				
	0 PLC ±-	±2°	PRODUCT SPEC 108-60133				
	1 PLC ±-						
2 PLC ±0.20	APPLICATION SPEC 114-60030						
3 PLC ±0.10							
4 PLC ±-							
MATERIAL	FINISH	WEIGHT	SIZE CAGE CODE DRAWING NO RESTRICTED TO				
-	-	-	A2 00779 C=2359366				
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 OF 5	REV B3


NAME					MINI COOL EDGE 10 INTEGRATED CONN.				
					0.6 PITCH, VERTICAL STANDARD				
					8X, SMT TYPE, 920HM				
SIZE		CAGE CODE		DRAWING NO			RESTRICTED TO		
A2		00779		C-2359366					
				SCALE		SHEET		REV	
				10:1		2 OF 5		B3	




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MIKE 04JULY2019		TE Connectivity			
		CHK MICHAEL 04JULY2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MINI COOL EDGE IO INTEGRATED CONN. 0.6 PITCH, VERTICAL STANDARD 8X, SMT TYPE, 920HM			
		APVD MICHAEL 04JULY2019					
		PRODUCT SPEC 108-60133					
		APPLICATION SPEC 114-60030					
MATERIAL		FINISH		SIZE A2	CAGE CODE 00779	DRAWING NO C-2359366	RESTRICTED TO
-		-		WEIGHT -		SCALE 10:1	
-		-		CUSTOMER DRAWING		SHEET 2 of 5	
						REV B3	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



COMPONENTS KEEP OUT AREA
LIMITATION HEIGHT: 0mm
SCALE 6:1




COMPONENTS KEEP OUT AREA
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MIKE	04JULY2019	TE Connectivity		
DIMENSIONS:		CHK MICHAEL	04JULY2019			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MICHAEL	04JULY2019	NAME MINI COOL EDGE IO INTEGRATED CONN. 0.6 PITCH, VERTICAL STANDARD 8X, SMT TYPE, 920HM		
	0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES ±2°	PRODUCT SPEC 108-60133				
MATERIAL	FINISH	APPLICATION SPEC 114-60030		SIZE A2	CAGE CODE 00779	DRAWING NO C-2359366
-	-	WEIGHT -		RESTRICTED TO		
CUSTOMER DRAWING			SCALE 6:1	SHEET 3 OF 5	REV B3	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

RECOMMENDED AIC CARD DIMENSIONS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MIKE	04JULY2019	 TE Connectivity		
DIMENSIONS:		CHK MICHAEL	04JULY2019			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MICHAEL	04JULY2019	NAME MINI COOL EDGE IO INTEGRATED CONN.		
	0 PLC ±-	PRODUCT SPEC	108-60133	0.6 PITCH, VERTICAL STANDARD		
	1 PLC ±-	APPLICATION SPEC	114-60030	8X, SMT TYPE, 92OHM		
	2 PLC ±0.20			SIZE	CAGE CODE	DRAWING NO
	3 PLC ±0.10			A2	00779	C-2359366
	4 PLC ±-					
ANGLES	±5°					
MATERIAL	FINISH	WEIGHT	-			RESTRICTED TO
-	-	CUSTOMER DRAWING		SCALE	4:1	SHEET
						4 OF 5
						REV B3

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-

D

C

B

A

D

C

B

A








FIGURE 1
DIRECTION OFF TOP OF REEL
FOR USER UNREEING

SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MIKE	04JULY2019		TE Connectivity					
		CHK MICHAEL	04JULY2019							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MICHAEL	04JULY2019		NAME			
mm		0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES ±2°		PRODUCT SPEC 108-60133		MINI COOL EDGE IO INTEGRATED CONN. 0.6 PITCH, VERTICAL STANDARD 8X, SMT TYPE, 920HM				
				APPLICATION SPEC 114-60030		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		MATERIAL		FINISH		WEIGHT		A2 00779 C-2359366		
-		-		-		CUSTOMER DRAWING		SCALE 4:1	SHEET 5 OF 5	REV B3