

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	05MAY2022	LL	DZ

NOTES:
1. MATERIAS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS
CONTACT: COPPER ALLOY







2. FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100u".
UNDER PLATING: NICKEL PLATING 50u" MIN OVER ALL.
SHELL: UNDER PLATING: ELECTROLESS NICKEL PLATING 50u"MIN OVERALL.


3. HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-702.

4. TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.

5. PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.

6. TAPE AND REEL PACKAGED FOR PICK AND PLACE SMT PROCESSING.
SEE FIGURE 1. POCKET TAPE WIDTH = 44.



STANDARD CONSTRUCTION	450PCS	150PCS	W/ CAP	30u" GOLD	4.20MM	I-2359992-8	
					3.00MM	I-2359992-7	
					2.20MM	I-2359992-6	
					1.50MM	I-2359992-5	
				15u" GOLD	4.20MM	I-2359992-4	
					3.00MM	I-2359992-3	
					2.20MM	I-2359992-2	
					1.50MM	I-2359992-1	
				30u" GOLD	4.20MM	2359992-8	
					3.00MM	2359992-7	
					2.20MM	2359992-6	
					1.50MM	2359992-5	
	15u" GOLD	4.20MM	2359992-4				
		3.00MM	2359992-3				
		2.20MM	2359992-2				
		1.50MM	2359992-1				
OPTIONS	CARTON QUANTITY	REEL QUANTITY	CAP OPTION	△ 2	CONTACT FINISH	DIM A	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				TE Connectivity			
DIMENSIONS: mm		DWN 22JUL2019 LEO LI		NAME LOW PROFILE SLIM SAS X8, RECEPTACLE VERTICAL CONN.			
		CHK 22JUL2019 DAVID ZHANG					
		APVD 22JUL2019 DAVID ZHANG		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		PRODUCT SPEC					
		APPLICATION SPEC					
		FINISH					
MATERIAL SEE NOTE		WEIGHT		A2 00779 C-2359992			
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 3 REV A			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A

A



RECOMMENDED PCB LAYOUT
AND KEEP OUT AREA
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	
1 PLC	±0.20	
2 PLC	±0.15	
3 PLC	±0.10	
4 PLC	±	
ANGLES		±2°
FINISH	-	
	-	

DWN
LEO LI
22JUL2019

CHK
DAVID ZHANG
22JUL2019

APVD
DAVID ZHANG
22JUL2019

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING



TE Connectivity

NAME
LOW PROFILE SLIM SAS
X8, RECEPTACLE VERTICAL CONN.

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2359992	

SCALE	4:1	SHEET	2 OF 3	REV	A
-------	-----	-------	--------	-----	---

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 22JUL2019	TE Connectivity		
DIMENSIONS: mm		CHK DAVID ZHANG 22JUL2019			
		APVD DAVID ZHANG 22JUL2019	NAME LOW PROFILE SLIM SAS X8, RECEPTACLE VERTICAL CONN.		
		PRODUCT SPEC -	SIZE A2		
MATERIAL SEE NOTE		APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C-2359992	RESTRICTED TO
		WEIGHT -	SCALE 4:1 SHEET 3 OF 3 REV A		
		CUSTOMER DRAWING			