


P	LTR	DESCRIPTION	DATE	DWN	APVD
A3		PCN E-21-002058	12FEB2021	PN	GL
B		REVISED PER ECN-23-212192	04MAY2023	GB	GL
B1		REVISED PER ECN-23-215441	16MAY2023	RK	GL
B2		REVISED PER PCN-23-182586	19JUL2023	GB	IG



NOTES :

- PACKAGING:
ASSEMBLY IN TE STANDARD CARTON
 - ELECTRICAL TEST: 100% FOR SHORT CIRCUIT ACC. TE SPECIFICATION 108-18857. STANDARD TEST 3.1.1 a,b,d AND 3.1.2 d.e.m.
- △ LENGTH "L" ACCORDING TABLE IS FOR STRAIGHT CABLE.
- △ LABEL PRINT SEE LABEL LEGEND
- APPLICATION SPECIFICATION FOR enetSEAL 114-151045
APPLICATION SPECIFICATION FOR MCON 1.2 mm CONTACT SYSTEM 114-18464
INSTRUCTION SHEET FOR 1.2-mm MCON WIRE DRESS COVER 408-32185
- △ RETAINER PRESENT AND CLOSED.
- △ REFER LENGTH SCHEDULE.

LENGTH SCHEDULE △△

TE PN	REV	ALIAS PART NO	LENGTH L (mm)	TOL (mm)
2362354-1	A	UTPB-ESMSA-ESFSA-500	500	+20
2362354-2	B	UTPB-ESMSA-ESFSA-100	1000	+20
2362354-3	B	UTPB-ESMSA-ESFSA-1500	1500	+30
2362354-4	B	UTPB-ESMSA-ESFSA-3000	3000	+40
2362354-5	B	UTPB-ESMSA-ESFSA-5000	5000	+40

OBSOLETE

TABLE LEGEND: △


TE CONNECTIVITY : 
 TE PN : SEE TABLE
 REV : SEE TABLE
 YYCWD

WIRE COLOUR SCHEDULE (LOADING SIDE)

MCON 1.2 TAB	CAVITY#	SIDE A	SIDE B	MCON 1.2 RECEPTACLE
	1	WHITE	WHITE	
	2	BLUE	BLUE	

1	LABEL 60 X 50 MM	8
30 ± 5mm	RNF-100-1/4-6-SP (SHRINKING TUBE BLUE)	7
2	MCON WIRE DRESS COVER 2POS PLUG STRAIGHT	6
2	MCON1.2 CB TAB STC AG	5
1	INLINE CAP ASSEMBLY 2 POSITION SEALED	4
2	MCON 1.2 CB REC SRC AG	3
1	PLUG ASSEMBLY, SEALED, 2POSITION	2
△	2 POS. CABLE. 0.5 SQMM. ETHERNET. CHAMPLAIN	1
QTY	DESCRIPTION	ITEM NO.

PRODUCT CHARACTERISTICS ACC. QMP EMEA_12 BESONDERE MERKMALE NACH QMP EMEA_12		TOLERANCING ISO 8015 TOLERIERUNG ISO 8015
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:
MATERIAL		FINISH
-		-
-		-

 TE Connectivity

NAME: ENETSEAL+MALE TO FEMALECABLE ASSY

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-2362354 RESTRICTED TO: B2

SCALE: 2:1 SHEET: 1 OF 1