









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
5		ADD DIMENSIONS	02MAR2022	LL	DZ
6		ADD BLOCK WALLS	17JUN2022	LL	DZ
7		EOL 3-2360229-6	26AUG2023	WZ	DZ
A		AS PER ECN-25-314638	02APR2025	AD	JM


NOTES:
1. MATERIAS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS
CONTACT: COPPER ALLOY
DUST CAP: STAINLESS.

2. FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100u".
UNDER PLATING: NICKEL PLATING 50u" MIN OVER ALL.
SHELL: UNDER PLATING: ELECTROLESS NICKEL PLATING 50u"MIN OVERALL.
3. HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-702.

4. TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.
5. PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.
6. TAPE AND REEL PACKAGED FOR PICK AND PLACE SMT PROCESSING.
SEE FIGURE 1. POCKET TAPE WIDTH = 72MM.

750PCS	250PCS	W/O DUST CAP	STANDARD CONSTRUCTION	30u" GOLD	4.20MM	3-2360229-8		
					3.00MM	3-2360229-7		
					1.50MM	3-2360229-5		
				15u" GOLD	4.20MM	3-2360229-4		
					3.00MM	3-2360229-3		
					2.20MM	3-2360229-2		
			NO RESONANCE DAMPING	30u" GOLD	1.50MM	3-2360229-1		
					4.20MM	2-2360229-8		
					3.00MM	2-2360229-7		
				15u" GOLD	2.20MM	2-2360229-6		
					1.50MM	2-2360229-5		
					4.20MM	2-2360229-4		
		W/ DUST CAP	STANDARD CONSTRUCTION	30u" GOLD	3.00MM	2-2360229-3		
					2.20MM	2-2360229-2		
					1.50MM	2-2360229-1		
				15u" GOLD	4.20MM	1-2360229-8		
					3.00MM	1-2360229-7		
					2.20MM	1-2360229-6		
			NO RESONANCE DAMPING	30u" GOLD	1.50MM	1-2360229-5		
					4.20MM	1-2360229-4		
					3.00MM	1-2360229-3		
				15u" GOLD	2.20MM	1-2360229-2		
					1.50MM	1-2360229-1		
					4.20MM	2360229-8		
		CAP OPTION	OPTIONS	CONTACT FINISH	DIM A	PART NUMBER		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 17SEP2019	TE Connectivity			
DIMENSIONS:		CHK: DAVID ZHANG 17SEP2019				
mm		APVD: DAVID ZHANG 17SEP2019				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC				
0 PLC ±0.30		108-60134	APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
1 PLC ±0.20			RESTRICTED TO		A 00779 C=2360229	
2 PLC ±0.10			SCALE		6:1	
3 PLC ±0.10			SHEET		1 OF 3	
4 PLC ±0.10			REV		A	
ANGLES FINISH			CUSTOMER DRAWING			
MATERIAL SEE NOTES		WEIGHT -				
SEE NOTES						




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE: ±0.05
SCALE 12:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 17SEP2019		TE Connectivity	
DIMENSIONS: mm		CHK: DAVID ZHANG 17SEP2019		NAME: LOW PROFILE SLIM SAS RECEPTACLE VERTICAL X16, 124P	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: DAVID ZHANG 17SEP2019		SIZE: A	
0 PLC ±0.20		PRODUCT SPEC		CAGE CODE: 00779	
1 PLC ±0.15		APPLICATION SPEC		DRAWING NO: 2360229	
2 PLC ±0.15		WEIGHT: -		RESTRICTED TO: -	
3 PLC ±0.15		CUSTOMER DRAWING		SCALE: 6:1	
4 PLC ±0.15				SHEET: 2 OF 3	
ANGLE FINISH ±0.15				REV: A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SEE DETAIL A




A1



DETAIL A
SCALE 5:1

△ FIGURE 1
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SCALE 2:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 17SEP2019		
DIMENSIONS:		CHK: DAVID ZHANG 17SEP2019		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: DAVID ZHANG 17SEP2019	NAME: LOW PROFILE SLIM SAS RECEPTACLE VERTICAL X16, 124P	
	0 PLC ±0.20	PRODUCT SPEC	SIZE: A	
	1 PLC ±0.15	APPLICATION SPEC	CAGE CODE: 00779	
	2 PLC ±0.15	WEIGHT: -	DRAWING NO: 2360229	
	3 PLC ±0.15	CUSTOMER DRAWING	RESTRICTED TO: -	
MATERIAL: SEE NOTES	SEE NOTES	SCALE: 6:1	SHEET: 3 OF 3	REV: A