

© 2019 TE Connectivity. All Rights Reserved.

D

D

C

C

B


B

A

A

LENGTH SCHEDULE:

TE PART NO.	REV.	LENGTH L [mm]	TOL.	WEIGHT [g]
2362769-1	A	1000	+20	13
2362769-2	A	500	+20	7
2362769-3	A	1500	+20	19
2362769-4	A	2000	+25	25
2362769-5	A	9000	+40	109



WIRING SCHEDULE:

CAVITY-NO. CONNECTOR A	WIRE COLOUR
1	WHITE
2	GREEN

NOTES:

- 1 PACKAGING:
ASSEMBLY IN TE STANDARD CARTON
- 2 ACCURATE CAVITY ASSIGNMENT ACC. TE SPECIFICATION 108-18857.
- 3 DIMENSION OF LENGTH IS FOR STRAIGHT CABLE.
- 4 PRODUCT SPECIFICATION: 108-94568
- 5 JACKET PRINT: 100 Mbps MATENet UTP, TE-CZ, TE PN, REV., DATE CODE
(DCWYY= D: DAY OF WEEK; CW: CALENDAR WEEK; YY: LAST TWO DIGITS OF YEAR)
THE PRINT MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION.
- 6 RELEASED CABLE TYPES ACCORDING TE SPECIFICATION 114-94431. A4



1-2302450-1	1	MATENET, FEMALE INSERT MODUL, BLACK	4
1-1703930-1	2	NANOMQS, RECEPTACLE TERMINAL	3
2302452-1	1	MATENET, FIXATION ELEMENT	2
-	see table	2 POS. CABLE, 0.13 SQMM, UNSHIELDED, ETHERNET	1
TE PART NO.	QTY - X	DESCRIPTION	ITEM NO.

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).											
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).				DWN M. Zelch 26SEP2019		 TE Connectivity					
				CHK P. Riedel 26SEP2019							
				APVD T. Dirion 27SEP2019							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC see note 4		NAME MATENET, PIGTAIL, 100 MBPS UTP - -					
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC -							
		MATERIAL		FINISH		WEIGHT see table		SIZE A2	CAGE CODE 00779	DRAWING NO C=2362769	RESTRICTED TO -
				CUSTOMER DRAWING		SCALE 2:1		SHEET 1 of 1		REV A4	