


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
1		INITIAL RELEASE	26AUG2019	BM RH



1. ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTRICTED SUBSTANCES).
2. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
3. ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, AND SIGNAL INTEGRITY.
4. CABLE BEND RADIUS 5X BUNDLED CABLE OD.
5. SEE SHEET 2 AND 3 FOR WIRING SCHEMATIC.
6. CONNECTORS ARE GEN-Z COMPLIANT.

⁷ LABEL INFORMATION SHOWN BELOW:



8. CABLE CONNECTOR MATES WITH TE SLIVER RECEPTACLE P/N 2332141-X, OR 2332208-X.

500	1000 +10/-0	2361337-2
250	500 +10/-0	2361337-1
"M"	"L"	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 26AUG2019	STE TE Connectivity	
		CHK R. HENRY 26AUG2019		
DIMENSIONS:		APVD -	NAME SLIVER 2.0 1C 33AWG 100 OHM STRAIGHT TO STRAIGHT	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -	SIZE A2	
0 PLC ±		APPLICATION SPEC -	CAGE CODE A200779	
1 PLC ±0.5		WEIGHT -	DRAWING NO C-2361337	
2 PLC ±0.13		CUSTOMER DRAWING	RESTRICTED TO -	
3 PLC ±0.013		SCALE 1:1	SHEET 1 OF 3	
4 PLC ±0.0001			REV 1	
ANGLES ±				
FINISH				

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

PIN #	P1		WIRE TYPE	P2		PIN #
	PAIR #	DESIGNATION		DESIGNATION	PAIR #	
A1		GROUND	DISCRETE	GROUND		A1
A2		GROUND	DISCRETE	GROUND		A2
A3		GROUND	DISCRETE	GROUND		A3
A4		GROUND	DISCRETE	GROUND		A4
A5		GROUND	DISCRETE	GROUND		A5
A6		GROUND	DISCRETE	GROUND		A6
A7		SIDE BAND	DISCRETE	SIDE BAND		A7
A8		SIDE BAND	DISCRETE	SIDE BAND		A8
A9		SIDE BAND	DISCRETE	SIDE BAND		A9
A10		SIDE BAND	DISCRETE	SIDE BAND		A10
A11		SIDE BAND	DISCRETE	SIDE BAND		A11
A12		SIDE BAND	DISCRETE	SIDE BAND		A12
A13		GND		GND		A13
A14		CLK	DIFF PAIR	CLK		A14
A15		CLK	DIFF PAIR	CLK		A15
A16		GND		GND		A16
A17	0	PCIeTX	DIFF PAIR	PCIeTX	0	A17
A18	0	PCIe TX	DIFF PAIR	PCIe TX	0	A18
A19		GND		GND		A19
A20	1	PCIeTX	DIFF PAIR	PCIeTX	1	A20
A21	1	PCIe TX	DIFF PAIR	PCIe TX	1	A21
A22		GND		GND		A22
A23	2	PCIeTX	DIFF PAIR	PCIeTX	2	A23
A24	2	PCIe TX	DIFF PAIR	PCIe TX	2	A24
A25		GND		GND		A25
A26	3	PCIeTX	DIFF PAIR	PCIeTX	3	A26
A27	3	PCIe TX	DIFF PAIR	PCIe TX	3	A27
A28		GND		GND		A28

COMMONED

COMMONED

THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 26AUG2019	 TE Connectivity	
DIMENSIONS: mm 		CHK R. HENRY 26AUG2019		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±- FINISH -		APVD -	NAME SLIVER 2.0 1C 33AWG 100 OHM STRAIGHT TO STRAIGHT	
MATERIAL -		PRODUCT SPEC -	SIZE A200779	CAGE CODE C-2361337
		APPLICATION SPEC -	RESTRICTED TO -	
		WEIGHT -	SCALE 1:1 SHEET 2 OF 3 REV 1	
		CUSTOMER DRAWING		

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

P1	WIRE TYPE	P2	
		DESIGNATION	PAIR #
PIN #	PAIR #	DESIGNATION	PIN #
B1		12V POWER	B1
B2		12V POWER	B2
B3		12V POWER	B3
B4		12V POWER	B4
B5		12V POWER	B5
B6		12V POWER	B6
B7		SIDE BAND	B7
B8		SIDE BAND	B8
B9		SIDE BAND	B9
B10		SIDE BAND	B10
B11		3.3 AUX POWER	B11
B12		SIDE BAND	B12
B13		GND	B13
B14		CLK	B14
B15		CLK	B15
B16		GND	B16
B17	0	PCIeRX	B17
B18	0	PCIe RX	B18
B19		GND	B19
B20	1	PCIeRX	B20
B21	1	PCIe RX	B21
B22		GND	B22
B23	2	PCIeRX	B23
B24	2	PCIe RX	B24
B25		GND	B25
B26	3	PCIeRX	B26
B27	3	PCIe RX	B27
B28		GND	B28

COMMONED

COMMONED

THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 26AUG2019	 TE Connectivity	
DIMENSIONS: mm 		CHK R. HENRY 26AUG2019	NAME SLIVER 2.0 1C 33AWG 100 OHM STRAIGHT TO STRAIGHT	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±- FINISH -		APVD -	PRODUCT SPEC -	RESTRICTED TO -
MATERIAL -	WEIGHT -	APPLIC. SPEC -	SIZE A200779	DRAWING NO. C-2361337
CUSTOMER DRAWING		SCALE 1:1	SHEET 3 OF 3	REV 1