

- ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTICTED SUBSTANCES).
- NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
- ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, AND SIGNAL INTEGRITY.
- CABLE BEND RADIUS 5X BUNDLE CABLE OD.
- SEE SHEET 2 AND 3 FOR WIRING SCHEMATIC.
- CONNECTORS ARE GEN-Z COMPLIANT.

<sup>7</sup> LABEL INFORMATION SHOWN BELOW:

TE LOGO

DATE CODE & SERIAL #

COUNTRY OF ORIGIN

2361343-X

YYWWSSSS

MADE IN



TE P/N

BARCODE

(DATECODE/SERIAL#)

8. CABLE CONNECTOR MATES WITH TE SLIVER RECEPTACLE P/N 2331813-X, OR 2331814-X.

71.3	133.1 +10/-0	2361343-3
500	1000 +10/-0	2361343-2
250	500 +10/-0	2361343-1
("M")	"L"	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 27AUG2019	 TE Connectivity						
		CHK R. HENRY 27AUG2019							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD		NAME				
mm			-		SLIVER 2.0 2C 33AWG				
			PRODUCT SPEC		STRAIGHT TO RIGHT ANGLE				
			-		-				
			APPLICATION SPEC		-				
MATERIAL		FINISH	WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-		-	-		A200779	C-2361343		-	
-		-	CUSTOMER DRAWING				SCALE	SHEET	REV
							1:1	1 OF 3	B1

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20		REVISIONS	
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.			

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20		REVISIONS	
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.			