





LOC	DIST	REVISIONS					
DY	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			1	INITIAL RELEASE	10SEP2019	TX	DZ
			2	REVISED THE HOLD DOWN LENGHT	31OCT2019	TX	DZ

NOTES:

- 1 MATERIAL:
HOUSING: HIGH TEMP THERMOPLASTIC, UL94V-0,
COLOR:BLACK
CONTACT:COPPER ALLOY
BOARDLOCK:COPPER ALLOY
- 2 FINISH:
CONTACT AREA:MIN 0.76µm GOLD PLATING
SOLDERTAIL: MIN 2.54µm MATTE TIN PLATING
UNDERPLATE: MIN 1.27µm NICKEL PLATING
- 3 PIN #P4 AND #P12 ONLY
- 4 SOLDERTAIL TO BE 0.05 MAX ABOVE
AND 0.10 MAX BELOW DATUM E
- 5 1.33 MAX MEASURED AT DATUM C



SECTION H - H
SCALE 4:1



TRAY	YES	2362786-3
TAPE & REEL	YES	2362786-2
TRAY	NO	2362786-1
PACKAGING	PICK-UP CAP (1)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TIM XUE CHK DAVID ZHANG APVD		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±. ANGLES ±3° FINISH		NAME SAS/PCIE 4.0 (U.2/U.3) RECEPTACLE, 68POS	
		PRODUCT SPEC		APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO RESTRICTED TO A200779 C-2362786 -	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 2 REV 1	

