




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A8	ECR-23-165912	22FEB2023	TZ	SH
	A9	ECR-24-229754	12DEC2024	MRM	WY
	A10	ECR-24-230801	26DEC2024	MRM	WY
	A11	ECR-24-230961	31DEC2024	MRM	WY

D

C


B

A



RECOMMENDED BUS BAR LAYOUT
RECOMMENDED THICKNESS: 2mm MIN

- NOTES:
- $\triangle 1$ MATERIAL: COPPER ALLOY
 - $\triangle 2$ FINISH: SILVER PLAING.
 - $\triangle 3$ RECOMMENDED DRILL HOLE SIZE: $\varnothing 7.30\text{mm}$



1.75	39.15	1-2361493-7
1.75	83.00	1-2361493-6
1.75	30.65	1-2361493-5
1.75	18.60	1-2361493-4
1.75	17.50	1-2361493-3
1.75	99.50	1-2361493-1
1.75	59.00	1-2361493-0
1.75	81.00	2361493-9
1.75	31.15	2361493-8
1.75	73.85	2361493-7
1.75	27.25	2361493-6
1.75	56.55	2361493-5
1.75	35.00	2361493-4
1.75	26.00	2361493-3
1.75	26.15	2361493-2
1.75	35.85	2361493-1
DIM N	DIM L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY LI	16AUG2019	 TE Connectivity			
		CHK -	-				
DIMENSIONS: mm		APVD SUNY ZHAO	16AUG2019	NAME PIN SIZE 8.0mm PIN FLOATING ICCON INSERT			
		PRODUCT SPEC 108-128111		SIZE A2			
		APPLICATION SPEC 114-128112					
MATERIAL 		WEIGHT -		CAGE CODE 00779	DRAWING NO C-2361493	RESTRICTED TO -	
		CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 3	REV A11

D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

D

C

B




A

D


C

B


A



RECOMMENDED BUS BAR LAYOUT
RECOMMENDED THICKNESS: 2mm~3.8mm




WASHER, THICKNESS: 1.2mm
MATERIAL: STEEL, Zn PLATING OR EQUIVALENT



M5 SCREW WITH NYLOC
MATERIAL: STEEL, Zn PLATING OR EQUIVALENT




- NOTES:
- 1 MATERIAL: COPPER ALLOY
 - 2 FINISH: SILVER PLAING.
 - 3 RECOMMENDED DRILL HOLE SIZE: $\varnothing 7.30$ mm





PACKED WITH SCREW AND WASHER	1.75	43.40	5-2361493-1
REMARK	DIM N	DIM L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY LI	16AUG2019	TE Connectivity			
DIMENSIONS: mm		CHK -	-				
		APVD SUNY ZHAO	16AUG2019	NAME PIN SIZE 8.0mm PIN FLOATING ICCON INSERT			
		PRODUCT SPEC 108-128111		-			
		APPLICATION SPEC 114-128112		SIZE A2	CAGE CODE 00779	DRAWING NO C-2361493	RESTRICTED TO -
		MATERIAL 1	WEIGHT -	CUSTOMER DRAWING			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		FINISH 2		SCALE 4:1	SHEET 2 OF 3	REV A11	
0 PLC ± 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±0.0001 ±							

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED BUS BAR LAYOUT
RECOMMENDED THICKNESS: 1.5mm~3.8mm



- NOTES:
- 1 MATERIAL: COPPER ALLOY
 - 2 FINISH: SILVER PLAING.
 - 3 RECOMMENDED DRILL HOLE SIZE: Ø 7.30mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.30
2 PLC	±0.20
3 PLC	±0.10
4 PLC	±0.0001
ANGLES	±

FINISH
2

PACKED WITHOUT SCREW AND WASHERS
1.30

15.00

1-2361493-2

REMARK

DIM N

DIM L

PART NUMBER

DWN
ANDY LI
16AUG2019

CHK
-

APVD
SUNY ZHAO
16AUG2019

PRODUCT SPEC
108-128111

APPLICATION SPEC
114-128112

WEIGHT
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
3 OF 3

REV
A11

TE Connectivity

NAME
PIN SIZE 8.0mm PIN
FLOATING ICCON INSERT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2361493

RESTRICTED TO
-