






THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	--
© COPYRIGHT - BY -	ALL RIGHTS RESERVED.	

P		LTR	DESCRIPTION	DATE	OWN	APVD
		A	RELEASED	4-20-20	CT	DM




SCALE 5:1

1. SHELL FINISH: SELECTIVE PLATE 7.5µm MIN ZINC-NICKEL OVER 10.0µm MIN ELECTROLESS NICKEL ALL OVER.
2. ROHS COMPLIANT.
3. MATERIALS: ALUMINUM ALLOY, THERMOPLASTIC AND FLUORSILICONE .
4. ASSEMBLY ACCEPTS SIZE 23 PIN CONTACTS.
5. CONTACT CURRENT RATING 5 AMPS CRIMPED TO 22 AWG WIRES.
6. CONTACT REMOVAL TOOL, GLENAIR PART NUMBER 809-088.
7. CONNECTOR SHIPPED WITH DUST CAPS. (NOT SHOWN)
8. MARKINGS PER MIL-STD-202, METHOD 215.
9. CONTACT PINS ARE KITTED IN SEALED PLASTIC BAGS AND SHIPPED UN-ASSEMBLED TO CONNECTOR.
10. THIS DRAWING HAS UNLIMITED USAGE RIGHTS.



GROUND CONTACT
TE P/N 2226913-2
SCALE 5:1 
QTY: 2



SIGNAL CONTACT
TE P/N 2226913-1
 SCALE 5:1
QTY: 7

230		95		C		6		9		2367784-1	
B		A		KEYING		POSITIONS		REMARKS		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C. C. THOMAS CHK D. MILLER APVD D. MILLER		3-10-20 3-10-20 3-10-20		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG CONNECTOR ASSEMBLY, LOW FORCE, NETT WARRIOR -		SIZE A1		CASE CODE 00779		DRAWING NO C=2367784	
		108-32114 APPLICATION SPEC 408-163015		PRODUCT SPEC 108-32114 APPLICATION SPEC 408-163015		WEIGHT -		RESTRICTED TO -		REV A	
MATERIAL -		FINISH -		CUSTOMER DRAWING		SCALE 8:1		SHEET 1		OF 1	