


ISO VIEW
(SCALE 1:1)



SECTION A-A

CODE	CODE A	CODE B
P/N	2365882-2/9-2365882-2(BI)	1-2365882-1
SHAPE		

KEY CODE TABLE

NOTE


1. GENERAL TOLERRANCE: ± 0.3 , $\pm 3^\circ$
2. BURR, SINK, FLASH MAX. 0.3 PERMISSIBLE
3. MATING PLUG ASS'Y P/N: X-2365978-X

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH
MATERIAL SEE TABLE	SEE TABEL

DWN BH LEE		
CHK DG JEONG		
APVD YJ YOUN	NAME 025 36P HEADER ASSY -SMD	
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING	DRAWING NO. C-2365882	RESTRICTED TO -
SCALE 2:1		SHEET 1 OF 1
		REV BI

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BI	REVISED (ECR-21-123877)	14DEC2021	BH	YJ



INFORMATION FOR PCB LAYOUT
*RECOMMENDED METAL MASK THICKNESS T=0.15 OVER.
*METAL MASK DIM. CAN CHANGE BY SOLDERING CONDITION.

NO.	COLOR/FINISH	MATERIAL	DESCRIPTION	QT'Y
4	TIN PLATED	COPPER ALLOY	SOLDER PEG	2 2 2
3	TIN PLATED	BRASS	025 TAB SMD LONG	18 18 18
2	TIN PLATED	BRASS	025 TAB SMD	18 18 18
1	NATURAL	LCP-GF30	025 36P HEADER HSG(B)	- 1 -
	BLACK	LCP-GF30	025 36P HEADER HSG(A)	1 - 1