



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED (ECR-24-212975)	26 JUN '24	JW	KT
	A5	REVISED (ECR-25-239355)	31 MAR 2025	DH	KT
	A6	REVISED (ECR-25-240357)	04 APR 2025	DH	KT




A6 2366531-2 AS SHOWN



NOTE

- GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
- MATERIAL: CuNiSi
- FINISH: PRE-TINNED
- THIS PRODUCT IS DESIGNED TO BE COMPATIBLE WITH UN-SEALED APPLICATIONS.
- APPLICATOR FEED: 7.5MM

SEE THE SHEET 2 OF 2 FOR DETAIL	$\phi 1.1-1.7$	$0.3-0.5 \text{ mm}^2$			025K REC L/I(S)	5-2366531-2
	$\phi 0.9-1.05$	$0.13-0.22 \text{ mm}^2$			025K REC L/I(SS)	5-2366531-1
SEE THE SHEET 1 OF 2 FOR DETAIL	$\phi 1.1-1.7$	$0.3-0.5 \text{ mm}^2$			.025K REC (S)	2366531-2
	$\phi 0.9-1.05$	$0.13-0.22 \text{ mm}^2$			.025K REC (SS)	2366531-1
NOTE	INSULATION RANGE	WIRE RANGE (NOMINAL SIZE)	FINISH	MATERIAL	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JW SEO		 TE Connectivity	
		CHK KT JUNG			
DIMENSIONS: mm		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± ± ± ± ± ±		NAME 025K RECEP CONTACTS	
				APVD YJ YOUN	
		PRODUCT SPEC 108-160296		SIZE A3	
		APPLICATION SPEC 114-61030			
MATERIAL		FINISH		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-2366531	
SEE TABLE		SEE TABLE		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1	
				SHEET 1 OF 2	
				REV A6	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



5-2366531-2 AS SHOWN

NOTE

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. MATERIAL: CuNiSi
3. FINISH: PRE-TINNED
4. 5- VARIANTS FOR NEW APPLICATION
5. APPLICATOR FEED: 7.5MM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity NAME 025K RECEP CONTACTS SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		CHK				
		APVD				
		PRODUCT SPEC				
		APPLICATION SPEC				
		WEIGHT				
CUSTOMER DRAWING		SCALE		SHEET		REV
		10:1		2 OF 2		A6