







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	Initial Release	25APR2023	NW S	JW H
	E5	ECR-23-187176	15SEP2023	NR	DJ
	F2	ECR-24-211737	13JUN2024	NR	DJ



SECTION Y-Y
SCALE 20:1




ISOMETRIC VIEW
SCALE 8:1



SECTION W-W
SCALE 20:1

- 1 MATERIAL: COPPER ALLOY, MATERIAL THICKNESS: 0.15mm
- 2 FINISH: 0.38µm MIN GOLD PLATE AT MATING INTERFACE FLASH IN REST OF GOLD PLATE ZONE
1µm - 3µm TIN IN LOCALIZED TIN PLATE ZONE
ALL OVER 1.27µm MIN NICKEL.
3. 2368012-1 AS SHOWN.
4. PACKAGED ON REEL.

DACAR 686-3, DACAR 585-3, G&G X9305, G&G X9534	2368012-1
APPLICABLE CABLE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NWS	02FEB2021	 TE Connectivity		
DIMENSIONS: mm		CHK NWS	02FEB2021			
		APVD JWH	02FEB2021	NAME CENTER CONTACT, FEMALE, 180 DEGREE, GEMNET		
		PRODUCT SPEC	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	114-32334	SIZE	CAGE CODE	DRAWING NO
0 PLC ±		WEIGHT	-	A2	00779	C=2368012
1 PLC ±		CUSTOMER DRAWING		SCALE	10:1	SHEET 1 OF 1
2 PLC ±						REV F2
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						
1						
2						