



① SUBASSY SOCKET OUTER CONTACT (5:1)




UNWINDING DIRECTION




DIE FEED 15.0mm ±0.05

② SOCKET CENTER CONTACT (8:1)




UNWINDING DIRECTION




DIE FEED 4.5mm±0.05

③ FERRULE (10:1)




UNWINDING DIRECTION




DIE FEED 12.0mm±0.05

NOTE

- △ WEIGHT WITHOUT CARRIER STRIP
- △ CONTACT KIT PART NUMBER FOR REFERENCE ONLY COMPONENTS MUST BE PURCHASED SEPARATELY
- △ ALLOWED AREA FOR CONTACT GRIPPING FOR CABLE TERMINATION
- △ DURING THE PROCESSING, THE CONTACT MAY BE LOADED WITH MAX. 30N IN AXIAL DIRECTION
- △ P/N IN () IS AN ALTERNATIVE P/N

2370897-2	I	2339392-1	A	FERRULE 1.5DS-CV		CuSn	Pre-Tin	0.38	3
	I	1-2389399-1	A	SOCKET CENTER CONTACT		CuSn	Au	0.02	2
	I	2298494-1	A	SUBASSEMBLY SOCKET CONTACT RG174	SOCKET OUTER CONTACT	CuSn	Pre-Tin	0.36	1
					DIELECTRIC	PBT	Blue RAL 5012 Similar		
2370897-1	I	2339392-1	A	FERRULE 1.5DS-CV		CuSn	Pre-Tin	0.38	3
	I	 2389399-1 (2298496-1)	A	SOCKET CENTER CONTACT		CuSn	Ag	0.02	2
	I	2298494-1	A	SUBASSEMBLY SOCKET CONTACT RG174	SOCKET OUTER CONTACT	CuSn	Pre-Tin	0.36	1
					DIELECTRIC	PBT	Blue RAL 5012 Similar		
CONTACT KIT PART NUMBER	Q'TY	 PART NUMBER	REV	DESCRIPTION		MATERIAL	FINISH	WEIGHT (g)	ITEM Pos
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN SM. RYU	-	 TE Connectivity			
				CHK GC. KWON	-				
				APVD GC. KWON	-				
				PRODUCT SPEC 108-61456	-				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-61258		NAME SOCKET CONTACT KIT, UNASSEMBLED MATE-H FOR 1.5DS-CV			
		0 PLC ±0.2 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±. 4 PLC ±. ANGLES ±°		WEIGHT -		SIZE A2		RESTRICTED TO -	
MATERIAL - -		FINISH -		CUSTOMER DRAWING		CAGE CODE 00779		DRAWING NO G=2370897	
						SCALE 5:1		SHEET 1 OF 2	
								REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET I			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	SM. RYU	-	TE Connectivity			
		CHK	GC. KWON	-				
		APVD	GC. KWON	-	NAME SOCKET CONTACT KIT, UNASSEMBLED MATE-H FOR 1.5DS-CV			
		PRODUCT SPEC	108-94515	-				
		APPLICATION SPEC	114-61258	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	-	-	A2	00779	C-2370897	-
		CUSTOMER DRAWING			SCALE	5:1	SHEET	2 OF 2
							REV	A