

© 2020 TE Connectivity. All Rights Reserved.

[illegible]

HWIL TERMINAL PN	PRODUCT GROUP DRAWING	APPLICABLE WIRE SIZE
5-1418758-3	1418754	0.35mm ²
5-1418760-3	1418754	0.5mm ²

5. GENERAL SPEC:

- 1). WORKING TEMP: -40-140°C;
- 2). WORKING VOLTAGE: 1000VDC;
- 3). DEGREE OF PROTECTION: IPX8, IP6K9K, IP67;
- 4). FLAMMABILITY: UL94 V-0;

6. HEADER ASSEMBLED TO THE AGGREGATE WITH 2 PIECES M5 SCREW:
THE SCREW HEAD DIAMETER < 9mm. THE DIAMETER OF WASHER 9-11mm;
RECOMMENDED TIGHTENING TORQUE IS 6±0.5NM;

	COORDINATE "X"	COORDINATE "Y"	DIAMETER "d"	DEPTH			
CODING "A"	+18.9 ± 0.05	+7.225 ± 0.05	4.85 ± 0.05	3.65 MIN			
CODING "B"	+18.9 ± 0.05	-7.225 ± 0.05					
CODING "C"	+19.8 ± 0.05	-6.55 ± 0.05	2.65 ± 0.05				
	-19.8 ± 0.05						
CODING "D"	+19.8 ± 0.05	+6.55 ± 0.05					
		-6.55 ± 0.05					
CODING "E"	+18 ± 0.05	-7.9 ± 0.05					
	-18 ± 0.05						
CODING "F"	+18 ± 0.05	+7.9 ± 0.05					
		-7.9 ± 0.05					

[illegible]