



P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED PER ECN-22-173278	13SEP2022	N.H	L.C
A1		REVISED PER ECR-24-198337	29JAN2024	N.H	L.C









KEYING A SHOWN FOR 5 POSITION




KEYING B SHOWN FOR 5 POSITION




KEYING C SHOWN FOR 5 POSITION



5 POS KEY C  
SCALE 5:1



SCALE 5:1  
5 POS KEY A



SCALE 5:1  
5 POS KEY B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	TE Connectivity			
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION SGI 1.25			
0 PLC ±- 1 PLC ±0.30 2 PLC ±0.15 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		PRODUCT SPEC 108-106451	SIZE A2	CAGE CODE 00779	DRAWING NO C-2371404	RESTRICTED TO -
MATERIAL 		APPLICATION SPEC 114-106497	SCALE 10:1		SHEET 1 OF 6	REV A1
		CUSTOMER DRAWING				

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

KEYING ILLUSTRATION

POS	KEY	KEY A	KEY B	KEY C
7-18 POS				
2-6 POS				

- 1 MATERIAL: NYLON, UL94V-0, COLOR: SEE TABLE.
- 2 APPLICABLE CONTACT P/N: 2371403-1.
- 3 RECOMMENDED MATING PART: SEE TABLE.
- 4 DIMENSIONS SHOW REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION	
0 PLC ±		PRODUCT SPEC 108-106451	SGI 1.25	
1 PLC ±0.30		APPLICATION SPEC 114-106497	SIZE A2	CAGE CODE 00779
2 PLC ±0.15		WEIGHT -	DRAWING NO C-2371404	RESTRICTED TO -
3 PLC ±		CUSTOMER DRAWING	SCALE 5:1	SHEET 2 OF 6
4 PLC ±				REV A1
ANGLES ±				
FINISH -				

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


WIRE RANGE	MATING HEADER RA	MATING HEADER VT	DIM C	DIM B	DIM A	POS	KEYING	COLOR	PLUG PART NO
26-30AWG	2360538-2	2360540-2	3.85	1.25	6.23	2	A	NATURAL	2371404-2
	2360538-3	2360540-3	5.10	2.50	7.00	3			2371404-3
	2360538-4	2360540-4	6.35	3.75	8.25	4			2371404-4
	2360538-5	2360540-5	7.60	5.00	9.50	5			2371404-5
	2360538-6	2360540-6	8.85	6.25	8.85	6			2371404-6
	2360538-7	2360540-7	10.10	7.50	10.10	7			2371404-7
	2360538-8	2360540-8	11.35	8.75	11.35	8			2371404-8
	2360538-9	2360540-9	12.60	10.00	12.60	9			2371404-9
	1-2360538-0	1-2360540-0	13.85	11.25	13.85	10			1-2371404-0
	1-2360538-1	1-2360540-1	15.10	12.50	15.10	11			1-2371404-1
	1-2360538-2	1-2360540-2	16.35	13.75	16.35	12			1-2371404-2
	1-2360538-3	1-2360540-3	17.60	15.00	17.60	13			1-2371404-3
	1-2360538-4	1-2360540-4	18.85	16.25	18.85	14			1-2371404-4
	1-2360538-5	1-2360540-5	20.10	17.50	20.10	15			1-2371404-5
	1-2360538-6	1-2360540-6	21.35	18.75	21.35	16			1-2371404-6
	1-2360538-7	1-2360540-7	22.60	20.00	22.60	17			1-2371404-7
	1-2360538-8	1-2360540-8	23.85	21.25	23.85	18			1-2371404-8
	2-2360538-2	2-2360540-2	3.85	1.25	6.23	2	B	BLACK	2-2371404-2
	2-2360538-3	2-2360540-3	5.10	2.50	7.00	3			2-2371404-3
	2-2360538-4	2-2360540-4	6.35	3.75	8.25	4			2-2371404-4
	2-2360538-5	2-2360540-5	7.60	5.00	9.50	5			2-2371404-5
	2-2360538-6	2-2360540-6	8.85	6.25	8.85	6			2-2371404-6
	2-2360538-7	2-2360540-7	10.10	7.50	10.10	7			2-2371404-7
	2-2360538-8	2-2360540-8	11.35	8.75	11.35	8			2-2371404-8
	2-2360538-9	2-2360540-9	12.60	10.00	12.60	9			2-2371404-9
	3-2360538-0	3-2360540-0	13.85	11.25	13.85	10			3-2371404-0
	3-2360538-1	3-2360540-1	15.10	12.50	15.10	11			3-2371404-1
	3-2360538-2	3-2360540-2	16.35	13.75	16.35	12			3-2371404-2
	3-2360538-3	3-2360540-3	17.60	15.00	17.60	13			3-2371404-3
	3-2360538-4	3-2360540-4	18.85	16.25	18.85	14			3-2371404-4
	3-2360538-5	3-2360540-5	20.10	17.50	20.10	15			3-2371404-5
	3-2360538-6	3-2360540-6	21.35	18.75	21.35	16			3-2371404-6
	3-2360538-7	3-2360540-7	22.60	20.00	22.60	17			3-2371404-7
	3-2360538-8	3-2360540-8	23.85	21.25	23.85	18			3-2371404-8
	4-2360538-2	4-2360540-2	3.85	1.25	6.23	2	C	RED	4-2371404-2
	4-2360538-3	4-2360540-3	5.10	2.50	7.00	3			4-2371404-3
	4-2360538-4	4-2360540-4	6.35	3.75	8.25	4			4-2371404-4
	4-2360538-5	4-2360540-5	7.60	5.00	9.50	5			4-2371404-5
	4-2360538-6	4-2360540-6	8.85	6.25	9.75	6			4-2371404-6
	4-2360538-7	4-2360540-7	10.10	7.50	11.00	7			4-2371404-7
	4-2360538-8	4-2360540-8	11.35	8.75	12.25	8			4-2371404-8
	4-2360538-9	4-2360540-9	12.60	10.00	13.50	9			4-2371404-9
	5-2360538-0	5-2360540-0	13.85	11.25	14.75	10			5-2371404-0
	5-2360538-1	5-2360540-1	15.10	12.50	16.00	11			5-2371404-1
	5-2360538-2	5-2360540-2	16.35	13.75	17.25	12			5-2371404-2
	5-2360538-3	5-2360540-3	17.60	15.00	18.85	13			5-2371404-3
	5-2360538-4	5-2360540-4	18.85	16.25	19.75	14			5-2371404-4
	5-2360538-5	5-2360540-5	20.10	17.50	21.00	15			5-2371404-5
	5-2360538-6	5-2360540-6	21.35	18.75	22.25	16			5-2371404-6
	5-2360538-7	5-2360540-7	22.60	20.00	23.50	17			5-2371404-7
	5-2360538-8	5-2360540-8	23.85	21.25	24.75	18			5-2371404-8

- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**
- OBSELETE**


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	 TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.30 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION SGI 1.25	
MATERIAL		PRODUCT SPEC 108-106451	RESTRICTED TO	
		APPLICATION SPEC 114-106497	SIZE A2	CAGE CODE 00779
		WEIGHT	DRAWING NO C-2371404	SCALE 10:1
		CUSTOMER DRAWING	SHEET 3 OF 6	REV A1

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-


KEY A SHOWN FOR ALL POSITIONS




2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION




8 POSITION




9 POSITION




10 POSITION




11 POSITION




12 POSITION




13 POSITION




14 POSITION




15 POSITION




16 POSITION



17 POSITION




18 POSITION


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	 TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION SGI 1.25	
0 PLC ±-		PRODUCT SPEC 108-106451	SIZE A2	
1 PLC ±0.30		APPLICATION SPEC 114-106497	CAGE CODE 00779	DRAWING NO C-2371404
2 PLC ±0.15		WEIGHT -	RESTRICTED TO -	
3 PLC ±-		CUSTOMER DRAWING	SCALE 5:1	SHEET 4 OF 6
4 PLC ±-				REV A1
ANGLES ±-				
FINISH ±-				
MATERIAL -				

KEY B SHOWN FOR ALL POSITIONS


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-




2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION




8 POSITION




9 POSITION




10 POSITION




11 POSITION




12 POSITION




13 POSITION




14 POSITION




15 POSITION




16 POSITION



17 POSITION




18 POSITION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	 TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.30 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION SGI 1.25	
MATERIAL -		PRODUCT SPEC 108-106451	SIZE A2	CAGE CODE 00779
		APPLICATION SPEC 114-106497	DRAWING NO C-2371404	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 5:1	SHEET 5 OF 6
			REV A1	


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


KEY C SHOWN FOR ALL POSITIONS




2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION




8 POSITION




9 POSITION




10 POSITION




11 POSITION




12 POSITION




13 POSITION




14 POSITION




15 POSITION




16 POSITION



17 POSITION



18 POSITION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO CHEN 24MAR2020	 TE Connectivity	
DIMENSIONS: mm		CHK DANIEL ZHANG 24MAR2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.30 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		APVD DANIEL ZHANG 24MAR2020	NAME PLUG HOUSING, CRIMP VERSION SGI 1.25	
MATERIAL -		PRODUCT SPEC 108-106451	SIZE A2	CAGE CODE 00779
		APPLICATION SPEC 114-106497	DRAWING NO C-2371404	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 5:1	SHEET 6 OF 6
			REV A1	