

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED(ECR-21-117663)	19OCT2021	JY	YJ
	A2	REVISED(ECR-21-119025)	17JAN2022	JY	YJ
	A3	REVISED(ECR-22-134856)	08APR2022	JY	YJ
	A4	REVISED(ECR-23-164947)	01FEB2023	JY	KT




TABLE-2






TABLE-1



NOTE
1. GENERAL TOLERANCE : $\pm 0.3, \pm 3^\circ$
2. RECOMMENDED METAL MASK THICKNESS = Min. 0.15mm
3. METAL MASK DIM, CAN BE CHANGED BY SOLDERING CONDITION
4. DATE CODE
5. THE MATING PLUG ASS'Y P/N : 2379274-1, 1-2379274-2

5	TIN	COPPER ALLOY	SOLDER PEG	2	2	2	2
4	TIN	COPPER ALLOY	0.64mm TAB(S)	12	12	12	12
3	TIN	COPPER ALLOY	0.64mm TAB(L)	12	12	12	12
2	BLACK	PCT-GF30	24P HEADER HSG CODE B	1	1	-	-
1	NATURAL	PCT-GF30	24P HEADER HSG CODE A	-	-	1	1
NO COLOR/FINISH				DESCRIPTION			
				Q'TY			



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

$\pm$
 $\pm$
 $\pm$
 $\pm$
 $\pm$
 $\pm$
 $\pm$

DWN
JY BAE

CHK
KT JUNG

APVD
YJ YOUN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
SMD 025 24P HEADER ASSY V-TYPE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2379263

RESTRICTED TO

SCALE
3:1

SHEET
1

OF
1

REV
A4