






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	24 JAN2022	SCB	PS



2385011-3 AS SHOWN



RECOMMENDED PCB LAYOUT

NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : COPPER ALLOY, TIN PLATED
2. ELECTRICAL
RATED CURRENT AND VOLTAGE : 20AMP 300V(UG B/C)
: 5AMP 600V(UG D)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 4 TOLERANCE NOT CUMULATIVE

90.62	12	1-2385011-2
83.00	11	1-2385011-1
75.38	10	1-2385011-0
67.76	9	2385011-9
60.14	8	2385011-8
52.52	7	2385011-7
44.90	6	2385011-6
37.28	5	2385011-5
29.66	4	2385011-4
22.04	3	2385011-3
14.42	2	2385011-2
DIM A	POS	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 JAN2022 SHRIC HARANA B	TE Connectivity		
		CHK 24 JAN2022 SUBHASREE S			
		APVD 24 JAN2022 PRASHANTH S	NAME TERMINAL BLOCK, 90 DEG HEADER, 7.62mm PITCH, TAIL LENGTH 3.1 mm		
DIMENSIONS: mm		PRODUCT SPEC 108-32299	SIZE A 3		CAGE CODE 00779
		APPLICATION SPEC 114-32242	DRAWING NO C-2385011		RESTRICTED TO -
MATERIAL 1		FINISH 1	WEIGHT -		
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A