



D

C

B

A





- 1 FINISH: OLIVER DRAB, CADMIUM.
- 2 FINISH: NICKEL, ELECTROLESS
- 3 REFERENCE MIL-DTL-38999 SPECIFICATION FOR PANEL NUT INSTALLATION TORQUE VALUE.
- 4 FINISH: NICKEL PTFE


45 DEGREE
INSERT OPTION

B

A



RECOMMENDED PANEL CUT-OUT 3



KEYING ORIENTATION	A	B	C	D
N	95°	141°	208°	236°
A	113°	156°	182°	292°
B	90°	145°	195°	252°

KEYING ORIENTATION DETAIL

NICKEL PTFE	4	B	45°	1-2379927-8
NICKEL PTFE	4	B	-	1-2379927-7
NICKEL PTFE	4	A	45°	1-2379927-6
NICKEL PTFE	4	A	-	1-2379927-5
NICKEL PTFE	4	N	45°	1-2379927-4
NICKEL PTFE	4	N	-	1-2379927-3
NICKEL	2	B	45°	1-2379927-2
NICKEL	2	B	-	1-2379927-1
OLIVE DRAB	1	B	45°	1-2379927-0
OLIVE DRAB	1	B	-	2379927-9
NICKEL	2	A	45°	2379927-8
NICKEL	2	A	-	2379927-7
OLIVE DRAB	1	A	45°	2379927-6
OLIVE DRAB	1	A	-	2379927-5
NICKEL	2	N	45°	2379927-4
NICKEL	2	N	-	2379927-3
OLIVE DRAB	1	N	45°	2379927-2
OLIVE DRAB	1	N	-	2379927-1
FINISH (SHELL AND NUT)		KEYING ORIENTATION SEE DETAIL	INSERT ORIENTATION	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN 20NOV2020		TE Connectivity	
DIMENSIONS:		CHK -		NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -		KIT, RECEPTACLE CONNECTOR ASSEMBLY	
	0 PLC ±°	PRODUCT SPEC		FIBER OPTIC, MT, SIZE 13, 2 CAVITY	
	1 PLC ±°	-		38999 STYLE, PANEL MOUNT	
	2 PLC ±0.13	APPLICATION SPEC		SIZE	
	3 PLC ±0.013	-		CAGE CODE	
	4 PLC ±°	-		DRAWING NO	
ANGLES ±°	FINISH	WEIGHT -		RESTRICTED TO	
MATERIAL	-	CUSTOMER DRAWING		A 00779 C=2379927	
-	-	SCALE 2:1		SHEET 1 OF 1	
-	-	REV A			