



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

HARD TRAY	330X235X19.3	30u"	45.0	8	44.5	70	72.45	89	71.65	164	7-2384030-4
HARD TRAY	330X235X19.3	30u"	86.5	8	44.5	70	72.45	89	71.65	164	5-2384030-8
HARD TRAY	330X235X19.3	30u"	53.5	8	28	37	39.45	56	38.65	98	5-2384030-7
SOFT TRAY	338X235X20.3	30u"	36.5	8	19.5	20	22.45	39	21.65	64	5-2384030-6
SOFT TRAY	TBD	30u"	22.5	8	12.5	6	8.45	25	7.65	36	5-2384030-5
HARD TRAY	330X235X19.3	30u"	10.0	8	44.5	70	72.45	89	71.65	164	5-2384030-4
HARD TRAY	330X235X19.3	30u"	10.0	8	28	37	39.45	56	38.65	98	5-2384030-3
SOFT TRAY	338X235X20.3	30u"	10.0	8	19.5	20	22.45	39	21.65	64	5-2384030-2
SOFT TRAY	TBD	30u"	10.0	8	12.5	6	8.45	25	7.65	36	5-2384030-1
HARD TRAY	330X235X19.3	15u"	86.5	8	44.5	70	72.45	89	71.65	164	4-2384030-8
HARD TRAY	330X235X19.3	15u"	53.5	8	28	37	39.45	56	38.65	98	4-2384030-7
SOFT TRAY	338X235X20.3	15u"	36.5	8	19.5	20	22.45	39	21.65	64	4-2384030-6
SOFT TRAY	TBD	15u"	22.5	8	12.5	6	8.45	25	7.65	36	4-2384030-5
HARD TRAY	330X235X19.3	15u"	10.0	8	44.5	70	72.45	89	71.65	164	4-2384030-4
HARD TRAY	330X235X19.3	15u"	10.0	8	28	37	39.45	56	38.65	98	4-2384030-3
SOFT TRAY	338X235X20.3	15u"	10.0	8	19.5	20	22.45	39	21.65	64	4-2384030-2
SOFT TRAY	TBD	15u"	10.0	8	12.5	6	8.45	25	7.65	36	4-2384030-1
HARD TRAY	330X235X19.3	G/F	86.5	8	44.5	70	72.45	89	71.65	164	3-2384030-8
HARD TRAY	330X235X19.3	G/F	53.5	8	28	37	39.45	56	38.65	98	3-2384030-7
SOFT TRAY	338X235X20.3	G/F	36.5	8	19.5	20	22.45	39	21.65	64	3-2384030-6
SOFT TRAY	TBD	G/F	22.5	8	12.5	6	8.45	25	7.65	36	3-2384030-5
HARD TRAY	330X235X19.3	G/F	10.0	8	44.5	70	72.45	89	71.65	164	3-2384030-4
HARD TRAY	330X235X19.3	G/F	10.0	8	28	37	39.45	56	38.65	98	3-2384030-3
SOFT TRAY	338X235X20.3	G/F	10.0	8	19.5	20	22.45	39	21.65	64	3-2384030-2
SOFT TRAY	TBD	G/F	10.0	8	12.5	6	8.45	25	7.65	36	3-2384030-1
HARD TRAY	330X235X19.3	30u"		NA	44.5	70	72.45	89	71.65	164	2-2384030-4
HARD TRAY	330X235X19.3	30u"		NA	28	37	39.45	56	38.65	98	2-2384030-3
SOFT TRAY	338X235X20.3	30u"		NA	19.5	20	22.45	39	21.65	64	2-2384030-2
SOFT TRAY	TBD	30u"		NA	12.5	6	8.45	25	7.65	36	2-2384030-1
HARD TRAY	330X235X19.3	15u"		NA	44.5	70	72.45	89	71.65	164	1-2384030-4
HARD TRAY	330X235X19.3	15u"		NA	28	37	39.45	56	38.65	98	1-2384030-3
SOFT TRAY	338X235X20.3	15u"		NA	19.5	20	22.45	39	21.65	64	1-2384030-2
SOFT TRAY	TBD	15u"		NA	12.5	6	8.45	25	7.65	36	1-2384030-1
HARD TRAY	330X235X19.3	G/F		NA	44.5	70	72.45	89	71.65	164	2384030-4
HARD TRAY	330X235X19.3	G/F		NA	28	37	39.45	56	38.65	98	2384030-3
SOFT TRAY	338X235X20.3	G/F		NA	19.5	20	22.45	39	21.65	64	2384030-2
SOFT TRAY	TBD	G/F		NA	12.5	6	8.45	25	7.65	36	2384030-1
TYPE	L*W*H (TRAY PACKAGE)	PRECIOUS PLATING THICKNESS (TOTAL)	W	V	J	N	C	B	A	POS.	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS, YAN 14DEC2020	 TE Connectivity	
DIMENSIONS: mm		CHK MIKE, CHEN 14DEC2020		
		APVD HOPE, LU 14DEC2020	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.9 SOLDER TAB AND CENTER POST	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-160247	RESTRICTED TO	
0 PLC ±		APPLICATION SPEC	SIZE A2	CAGE CODE 00779
1 PLC ±0.3		WEIGHT	DRAWING NO C-2384030	SCALE 4:1
2 PLC ±0.20		CUSTOMER DRAWING	SHEET 2 OF 6	REV B
3 PLC ±0.050				
4 PLC ±				
ANGLES ±				
FINISH				

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



RECOMMENDED PCB LAYOUT



ADD-IN CARD EDGE-FINGER DIMENSION
 DEFAULT TOLERANCE ±0.13

164	85.20	70	72.45	72.15
98	52.20	37	39.45	39.15
64	35.20	20	22.45	22.15
36	21.20	6	8.45	8.15
POS.	DIM. E	DIM. F	DIM. G	DIM. H


THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ± ANGLES ± FINISH ±	DWN SANDERS YAN 14DEC2020 CHK MIKE CHEN 14DEC2020 APVD HOPE LU 14DEC2020	TE Connectivity	
MATERIAL		PRODUCT SPEC 108-160247	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.9 SOLDER TAB AND CENTER POST	
		APPLICATION SPEC	SIZE A2	CAGE CODE 00779
		WEIGHT	DRAWING NO. C-2384030	RESTRICTED TO
		CUSTOMER DRAWING	SCALE 6:1	SHEET 3 OF 6 REV B

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

FRONT VIEW




36POS AS SHOWN
SCALE 4:1

FRONT VIEW




64POS AS SHOWN
SCALE 4:1

FRONT VIEW




98POS AS SHOWN
SCALE 4:1



FRONT VIEW



164POS AS SHOWN
SCALE 4:1




MYLAR SIZE
SCALE 4:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS, YAN 14DEC2020	 TE Connectivity	
		CHK MIKE, CHEN 14DEC2020		
DIMENSIONS: mm		APVD HOPE, LU 14DEC2020	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.9 SOLDER TAB AND CENTER POST	
		PRODUCT SPEC 108-160247	SIZE A2	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC -	CAGE CODE C-2384030	DRAWING NO 108-160247
MATERIAL -		WEIGHT -	RESTRICTED TO -	SCALE 6:1
		CUSTOMER DRAWING	SHEET 4 OF 6	REV B

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



HARD TRAY: FOR 164POS
SCALE 1:2




HARD TRAY: FOR 98POS
SCALE 1:2


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS, YAN 14DEC2020	STE TE Connectivity	
		CHK MIKE, CHEN 14DEC2020		
DIMENSIONS: mm		APVD HOPE, LU 14DEC2020	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.9 SOLDER TAB AND CENTER POST	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-160247	RESTRICTED TO	
0 PLC ±		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
1 PLC ±0.3		WEIGHT -	DRAWING NO C-2384030	SCALE 6:1
2 PLC ±0.20		CUSTOMER DRAWING	SHEET 5 OF 6	REV B
3 PLC ±0.050				
4 PLC ±				
ANGLES ±				
FINISH -				

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



SOFT TRAY: FOR 64POS
 SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14DEC2020 SANDERS, YAN	 TE Connectivity				
DIMENSIONS: mm		CHK 14DEC2020 MIKE, CHEN					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 14DEC2020 HOPE, LU	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.9 SOLDER TAB AND CENTER POST				
0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-160247	SIZE A2	CAGE CODE 00779	DRAWING NO C-2384030	RESTRICTED TO -	
MATERIAL -		WEIGHT -	CUSTOMER DRAWING		SCALE 6:1	SHEET 6 OF 6	REV B