

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2014

© COPYRIGHT 2006

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	13JAN2021	MK	IG

D

 $.366 \pm 0.005$
[9.30 ± 0.12] $.447$
[11.35] $.169$
[4.29] $.866$
[22.00] $.128$
[3.25] $.555$
[14.10] 1.868
[47.45]

(35° CHAMFER)

 $.625 \pm 0.010$
[15.88 ± 0.25] $\varnothing 1.125^{+0.002}_{-0.000}$
[28.58^{+0.05}_{0.00}]

32

RECOMMENDED MOUNTING HOLE

 $.072 \pm 0.010$
[1.83 ± 0.25] $.103 \pm 0.010$
[2.62 ± 0.25] $\varnothing 1.013 \pm 0.005$
[25.73 ± 0.12] $\varnothing 1.116 \pm 0.005$
[28.35 ± 0.12] $\varnothing .964 \pm 0.005$
[24.49 ± 0.12] $\varnothing 1.260$
[32.00] $.061 \pm 0.005$
[1.55 ± 0.12] $.140 \pm 0.005$
[3.56 ± 0.12]

TE INTERNAL PN	DEUTSCH PN
2385287-1	DT04-4P-LE27

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF ONLY
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.50-0.50]



"E" IDENTIFIES E-SEAL.



MATERIAL: SHELL: PA66 GF15, BLACK; SEAL: VMQ.

2. THIS RECEPTACLE MATES WITH DT06-4S-XXXX
(XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

1. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN K. MUKESH 13JAN2021

CHK R. MESSENGER 13JAN2021

APVD I. GRANTCHAROVA 14JAN2021

PRODUCT SPEC

108-151009


APPLICATION SPEC

114-151009

WEIGHT

15.71g

CUSTOMER DRAWING

DIMENSIONS:
INCHES [mm]TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±.025 [0.64]
4 PLC	±
ANGLES	±0°30'0"

MATERIAL

FINISH

N/A

**TE**



TE Connectivity

NAME
4 WAY RECEPTACLE WITH O-RING
E-SEAL DT SERIES

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 4AFU8 C-2385287

SCALE 2:1 SHEET 1 OF 1 REV A



DATECODE

