

ELECTRICAL	MECHANICAL	ENVIRONMENTAL			
Impedance (Ohm): <u>50</u>	Interface Dimension <u>1.35mm male and</u> 1.0mm female	TEMPERATURE RANGE -55 ℃~+125 ℃			
Frequency Range: DC to 90GHz		ROHS COMPLIANT			
Voltage Rating (Peak) <u>@ Sea Level 150 V RMS</u> Insulation Resistance (MIN.) <u>5000 M ohms</u> Contact Resistance (mohms MAX) Center Contact <u>4.0</u> Outer Contact <u>1.0</u> Dielectric Withstand Voltage: <u>500 V RMS Max</u>	Force to Engage and Disengage Engage: N/A Disengage: N/A Center Cantact Captivation Axial (N) 26.0 MIN Radial (In/Oz) N/A Cable Retention Axial (Lbs) N/A Mating cycles 500 cycles				
Insertion Loss : TBD VSWR: < <u>1.35 @ DC ~ 90GHz</u>					

А

В

1	SHELL CONTACT PIN INSULATOR BODY		STAINLESS STEEL BERYLLIUM COPPER		PASSIVATION GOLD 20-50 u"/ NICKEL 30 u"			
1								
1				PEEK		N/A		
1			STAINLESS STEEL		PASSIVATION			
2385347-1	PART NUMBER			MATERIAL		PLATING		
THIS DRAWING IS A C	CONTROLLED DOCUMENT.	PENG ZHAI Chk Roger Song	28JAN2021 28JAN2021 G 28JAN2021		E TE	TE	Connectivi	ty
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2	± - PRODUCT SPEC ± 0.3		NAME 1.3	1.35mm Male to 1.0mm Female Adapter —			
MATERIAL	4 PLC ± - ANGLES ± 5°	 VEIGHT			drawing no	35347		RESTRICTED TO
_	_ (CUSTOMER [DRAWING			scale 1:1	SHEET 1 (DF 1 REV A

W 2385347

А