






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10NOV2022	N.J	Z.Z




RECOMMENDED PCB LAYOUT (T=1.6mm), ONLY FOR INFORMATION.
CUSTOMER IS RESPONSIBLE FOR LAYOUT.



4	PIN	COPPER ALLOY	0.76 µm MIN. Au OVER Ni ON INTERFACE END. 3 µm MIN. TIN OVER Ni ON SOLDER END.	2
3	DIELECTRIC	PBT	BLACK	1
2	SHIELD	COPPER ALLOY	10 µm MIN. Sn OVER Ni.	1
1	DIECAST	Zn ALLOY	3 µm MIN. Sn OVER Ni AND Cu.	1
ITEM	DESCRIPTION	MATERIAL	FINISH & COLOR	QUANTITY

- NOTES:
- MATED WITH DATA DT HEADER ASSY SEE DRAWING: 2386211.
 - TRAY PACKAGING.
 - TIP OF SOLDER TAIL CAN BE INSERTED INTO RECOMMENDED PCB (T=1.6).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.Ji 24APR2022	 TE Connectivity	
		CHK C.Wan 25APR2022		
		APVD Z.W.Zhou 26APR2022		
		PRODUCT SPEC		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME DT HIGH SPEED 90DEG HEADER TERMINAL	
		0 PLC ± 1 PLC ±0.30 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2°	APPLICATION SPEC	
		FINISH	WEIGHT	
MATERIAL			CUSTOMER DRAWING	
			SCALE 2:1	SHEET 1 OF 1
			DRAWING NO. A3 00779 C-2386215	RESTRICTED TO REV A