




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-22-153884	19SEP22	S.T	Z.Z
	A3	ECR-22-162330	28DEC22	S.T	Z.Z
	A4	ECN-23-223419	25JUL23	Y.L	Z.Z
	B	PCN-25-240976	05MAY25	S.T	Z.Z



- 1 MATERIAL: COPPER ALLOY
 2 MATERIAL: STEEL
 3. BULK PACKAGED



2387549-3	B	CRIMP ANVIL - 120mm ² (STANDARD)	1	(17.69)	Ø23.1	22.2	23.0
2387549-2	B	CRIMP ANVIL - 95mm ² (STANDARD)	1	(25.91)	Ø20.4	19.5	20.3
2387549-1	B	CRIMP ANVIL - 70mm ² (STANDARD & HIGH FLEX)	1	(33.84)	Ø17.4	16.7	17.3
PART NO.	PART REV.	DESCRIPTION	MATERIAL	WEIGHT(g)	DIA.A	MIN.	MAX.
						CABLE O.D.	

© 2021 TE Connectivity. All Rights Reserved.


DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±0.3

0 PLC ±
 1 PLC ±0.1
 2 PLC ±0.01
 3 PLC ±0.001
 4 PLC ±0.0001
 ANGLES ±

DWN
Y.L.I

25JUL2023

CHK
J.L.I

25JUL2023

APVD
Z.ZHOU

25JUL2023

PRODUCT SPEC

108-160407

APPLICATION SPEC

114-160223/160418

WEIGHT

MATERIAL



FINISH



TE Connectivity

NAME

CRIMP ANVIL
HVP-HD1400

SIZE

CAGE CODE

DRAWING NO

A 4

00779

C-2387549

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

2:1



SHEET

1 OF 2

REV

B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



	B	B	B				
2387549-8	B	CRIMP ANVIL - 95mm ² (HIGH FLEX)		(23.55)	$\varnothing 20.0$	19.1	19.9
2387549-7	B	CRIMP ANVIL - 120mm ² (HIGH FLEX)		(15.30)	$\varnothing 23.1$	22.2	23.0
2387549-4	B	CRIMP ANVIL - 150mm ² (HIGH FLEX)		(7.9)	$\varnothing 25.6$	24.5	25.5
PART NO.	PART REV.	DESCRIPTION	MATERIAL	WEIGHT(g)	DIA.A	MIN.	MAX.
						CABLE O.D.	

© 2021 TE Connectivity. All Rights Reserved.

DIMENSIONS:		DWN Y.LI	25JUL2023	MATERIAL		FINISH	
mm		CHK J.LI	25JUL2023	1 2			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Z.ZHOU	25JUL2023	TE		TE Connectivity	
± 0.3		PRODUCT SPEC	108-160407	NAME		CRIMP ANVIL HVP-HD1400	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES $\pm$ ± 0.1 ± 0.01 ± 0.001 ± 0.0001 $\pm$		APPLICATION SPEC	114-160223/160418	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A 4	00779	C-2387549		-
CUSTOMER DRAWING				SCALE	2:1	SHEET	2 OF 2
						REV	B