





AS SHOWN 2390858-2
SCALE 1:2




AC CAVITY BLOCKED

FOR MISSING DIM
REFER 2390858-2


AS SHOWN 2390858-1
SCALE 1:2



AS SHOWN 2390858-1
SCALE 1:2



AS SHOWN 2390858-2
SCALE 1:2




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		PCN-21-117035	11OCT2021	AS	KPB
B3		ECN-22-156556	30MAY2022	SS	KPB
B4		ECN-23-219930	28JUN2023	SS	KPB
B5		PCN-24-211741	13JUN2024	SS	KPB


NOTES

- TE-SINGLE PART NUMBER.
- REVISION, SEE TABLE (CHARACTERS ONLY).
- MATERIAL MARKING ACCORDING TO VDA 260.
- PRODUCTION DATE.
- TE-TRADEMARK ACC TO SPEC 1621426-4.
- SEALING SURFACES, NO FLASH, BURR OR GATEMARK ALLOWED.
- UNSPECIFIED GENERAL TOLERANCE TO BE $\boxed{0.6\text{ CZ}}$ ALL OVER UNLESS OTHERWISE STATED.
- PACKAGING ACCORDING TO V2390858.
- PREPARE AS CONVERSIONKIT IN TOOL




SECTION B-B



SECTION A-A
SCALE 1:2




AS SHOWN 2390858-4
SCALE 1:2




FOR MISSING DIM
REFER 2390858-4

AS SHOWN 2390858-3
SCALE 1:2




AC CAVITY BLOCKED


AS SHOWN 2390858-3
SCALE 1:2



AS SHOWN 2390858-4
SCALE 1:2



SECTION B-B



DIMENSION AND TOLERANCES ACCORDING TO:
Bemaßungen und Toleranzen gemäß:

DIN 16742
DIN EN ISO 8015 (A1) - DIN EN ISO 291
DIN EN ISO 14405-1/-2/-3

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.5
1 PLC	±0.13
2 PLC	±0.13
3 PLC	±0.013
4 PLC	±0.0001
ANGLES	±
FINISH	-
MATERIAL	SEE TABLE
	-

DWN	SUBHAS H	09JUN2021
CHK	DEEPAK M	09JUN2021
APVD	KASHYAP P B	09JUN2021
PRODUCT SPEC	108-94865	
APPLICATION SPEC	114-94757	
WEIGHT	-	
CUSTOMER DRAWING		

		TE Connectivity	
NAME			
CABLE EXIT			
-			
-			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2390858	-
SCALE 5:1		SHEET 1 OF 1	REV B5