




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





NOTE 1 GROUND CONNECTION:
DO NOT LOOSEN INNER GROUND NUTS.
M5 GROUND NUTS TYP. TORQUE (Nm): 7

NOTE 2 INPUT OUTPUT CONNECTION TERMINAL:
CONNECTION METHOD: SCREW CONNECTION WITH TENSION SLEEVE.
WIRE SIZE CROSS SECTION RANGE FLEXIBLE CONDUCTOR (mm²): 0.5 - 16
WIRE STRIP LENGTH (mm): 16
CONNECTOR TERMINAL SCREW TORQUE MIN - MAX (Nm): 2.0 - 2.3

THE ABOVE DATA IS FOR GUIDANCE/REFERENCE ONLY.
TERMINALS WILL ACCEPT A RANGE OF WIRE C.S.A. BUT WIRE SIZE USED SHOULD BE SUITABLE
FOR OPERATING CURRENT.

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BANGERA 08AUG2022		<div>TE Connectivity</div>					
		CHK C. BOLLE 08AUG2022							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±-		NAME 760V POWER LINE FILTER 30 AHV S BS					
				APVD L. IRUDHAYARAJ 08AUG2022					
MATERIAL		PRODUCT SPEC 2426169-1		SIZE A3					
		APPLICATION SPEC -							
		WEIGHT 4 Kgs		CAGE CODE 00779		DRAWING NO C-2405077-6			
		FINISH -		RESTRICTED TO -					
CUSTOMER DRAWING				SCALE 1:2		SHEET 2 OF 2		REV A	