





4826 13/13



SECTION D-D



SECTION A-A



1. MISSING DIMENSIONS ACC. TO 2399609-1

3-2399609-3	E	M	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	M	PA66-GF	AQUA RED	(315)	1	9
					-	-	-		-	1-8
3-2399609-2	E	L	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	L	PA66-GF	AQUA BROWN	(315)	1	9
					-	-	-		-	1-8
3-2399609-1	E	K	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	K	PA66-GF	AQUA GREEN	(315)	1	9
					-	-	-		-	1-8
2-2399609-9	E	J	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	J	PA66-GF	ORANGE	(315)	1	9
					-	-	-		-	1-8
2-2399609-8	E	H	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	H	PA66-GF	YELLOW	(315)	1	9
					-	-	-		-	1-8
2-2399609-7	E	G	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	G	PA66-GF	RED	(315)	1	9
					-	-	-		-	1-8
2-2399609-6	E	F	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	F	PA66-GF	BROWN	(315)	1	9
					-	-	-		-	1-8
2-2399609-5	E	E	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	E	PA66-GF	GREEN	(315)	1	9
					-	-	-		-	1-8
2-2399609-4	E	D	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	D	PA66-GF	PURPLE	(315)	1	9
					-	-	-		-	1-8
2-2399609-3	E	C	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	C	PA66-GF	BLUE	(315)	1	9
					-	-	-		-	1-8
2-2399609-2	E	B	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	B	PA66-GF	NATURE	(315)	1	9
					-	-	-		-	1-8
2-2399609-1	E	A	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 2-2399609-1	A	PA66-GF	BLACK	(315)	1	9
					-	PA66-GF	RED		1	8
					-	PA66-GF	BLACK		1	7
					-	SILICONE	RED		1	6
					-	PA10T MOLDING	-		1	5
					-	PA66-GF	BLACK		1	4
					-	PA66-GF	BLACK		1	3
					-	-	-		2	2
					-	AL-ALLOY	PASSIVATION		1	1
					-	-	SURFACE COLOR /TREATMENT			
TE-ASSY-NO	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	PASSIVATION	WEIGHT (g)	QTY	ITEM

1. MISSING DIMENSIONS ACC. TO 2399609-1

5-2399609-3	E	M	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	M	PA66-GF	AQUA RED	(315)	1	9
					-	-	-		-	1-8
5-2399609-2	E	L	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	L	PA66-GF	AQUA BROWN	(315)	1	9
					-	-	-		-	1-8
5-2399609-1	E	K	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	K	PA66-GF	AQUA GREEN	(315)	1	9
					-	-	-		-	1-8
4-2399609-9	E	J	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	J	PA66-GF	ORANGE	(315)	1	9
					-	-	-		-	1-8
4-2399609-8	E	H	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	H	PA66-GF	YELLOW	(315)	1	9
					-	-	-		-	1-8
4-2399609-7	E	G	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	G	PA66-GF	RED	(315)	1	9
					-	-	-		-	1-8
4-2399609-6	E	F	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	F	PA66-GF	BROWN	(315)	1	9
					-	-	-		-	1-8
4-2399609-5	E	E	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	E	PA66-GF	GREEN	(315)	1	9
					-	-	-		-	1-8
4-2399609-4	E	D	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	D	PA66-GF	PURPLE	(315)	1	9
					-	-	-		-	1-8
4-2399609-3	E	C	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	C	PA66-GF	BLUE	(315)	1	9
					-	-	-		-	1-8
4-2399609-2	E	B	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	B	PA66-GF	NATURE	(315)	1	9
					-	-	-		-	1-8
4-2399609-1	E	A	1POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING FOLLOW 4-2399609-1	A	PA66-GF	BLACK	(315)	1	9
					-	PA66-GF	RED		1	8
					-	PA66-GF	BLACK		1	7
					-	SILICONE	RED		1	6
					-	PA10T MOLDING	-		1	5
					-	PA66-GF	BLACK		1	4
					-	PA66-GF	BLACK		1	3
					-	-	-		2	2
					-	AL-ALLOY	PASSIVATION		1	1
					-	-	SURFACE COLOR /TREATMENT			
TE-ASSY-NO	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	PASSIVATION	WEIGHT (g)	QTY	ITEM

