

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	TE STANDARD	26AUG2024	NM	RB

NOTE
Bemerkungen:
1 TE-CONNECTIVITY ORDER-NUMBER
TE-Connectivity Bestellnummer

TECHNICAL DATA

HOUSING MATERIAL.....THERMOPLAST GF
PROTECTION INTERIOR.....IP40 DIN 40050
CONNECTIONS.....IP00 DIN 40050

TEMPERATUR RANGE..... -40°C TO +70°C

ELECTRICAL DATA
VOLTAGE RANGE:.....18 - 32 VDC
PULL IN CURRENT:1000 A AT 24 VDC
DUTY RATING:500 A AT 24 VDC
ELECTRICAL LIFE:10 000 CYCLES


Technische Daten
Aufbau

Gehaeuse.....Thermoplast GF
Schutzart Innenraum.....IP40 DIN 40050
Anschluesse.....IP00 DIN 40050

Umgebungstemperatur -40°C TO +70°C

Elektrische Daten

Spannungsbereich18 bis 32 VDC
Einschaltstrom1000 A bei 24 VDC
Dauerstrom500 A bei 24 VDC
Elektrische Lebensdauer10 000 Betaetigungen



ISO 1:5

K1070300	1	A	EMERG. MAINSWITCH 1000A NOT-Hauptschalter 1000A	1
TE ORDER-NO.	REV.		DESCRIPTION	ITEM NO



TE Connectivity

NAME
EMERG. MAINSWITCH 1000A
NOT-Hauptschalter 1000A

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=24-01-00-904	-

DWN	17NOV2000
CHK	17NOV2000
APVD	01AUG2001
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2867 cL
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±
MATERIAL	

CIRCUIT DIAGRAM
Schaltbild

