


VIEW CONNECTOR A



CIRCUIT LIST:

TE P/N	PIN	WIRE COLOR	"L"	CODE	PART REV.	PROJECT
2406228-1	1	BLUE/WHITE	4150 ⁺⁶⁰ ₀	I	A	S202
	2	BLACK/WHITE				
2406228-2	1	RED	4300 ⁺⁶⁰ ₀	I	A	S202
	2	YELLOW				







TABLE 2



CODE I



CODE II



CODE III

NOTE:

1 HARNESS TO BE 100% ELECTRICAL TEST ACCORDING TO TE SPECIFICATION 108-18857

CC 2 CRIMPING ACCORDING TO TE APPLICATION SPECIFICATION 114-18972

3. THE COVER FOR HOUSING MUST BE PUT TO THE PRE-ASSEMBLY POSITION AFTER ALL THE PINS HAVE BEEN INSERTED

4. TWISTED LENGTH L1: 20 ± 2 mm

5. MARKING TE P/N AND TRACKING INFORMATION ON CONNECTOR

"D" PART

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.GU	12JAN2022		 TE Connectivity	
		CHK T.GUO	12JAN2022			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P.WU	NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		CHANGAN S202 SQUIB AK2 90DEG PIGTAIL
				APPLICATION SPEC		
MATERIAL		FINISH		WEIGHT	SIZE	CAGE CODE
					A2	00779
					DRAWING NO	
					C=2406228	
					RESTRICTED TO	
					-	
CUSTOMER DRAWING					SCALE	SHEET
					1:1	1 OF 1
						REV
						A