



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED ECN-23-205302	30MAR2023	AG	TG

D

C

B

A



VIEW CONNECTOR A

CIRCUIT LIST:

TE P/N	PIN	WIRE COLOR	"L"	TE PART REV.
2410747-1	1	BLUE	1780±20	A
	2	BROWN		
2410747-2	1	YELLOW	1970±20	A
	2	GREY		
A1 2410747-3	1	BLUE	1995±20	A
	2	BROWN		
A1 2410747-4	1	YELLOW	6075±50	A
	2	GREY		

NOTE:

CC 1 HARNESS TO BE 100% ELECTRICAL TEST ACCORDING TO TE SPECIFICATION 108-18857

CC 2 CRIMPING ACCORDING TO TE APPLICATION SPECIFICATION 114-5234

3 THE COVER FOR HOUSING MUST BE PUT TO THE PRE-ASSEMBLY POSITION AFTER ALL THE PINS HAVE BEEN INSERTED

4 TWISTED LENGTH L1: 20±2mm

5. MARKING TE P/N AND DATE TRACKING INFORMATION ON CONNECTOR A

"D" PART

A/R	mm	—	TWISTED WIRE FLRY-A, 2*0.5mm ²	5
1	PC	353379-2	FERRITE	4
2	PC	353376-3	TERMINAL	3
1	PC	1612119-1	BUTTON	2
1	PC	1612120-1	HOUSING, YELLOW	1
QTY	UNIT	P/N	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.GU 25MAR2022	TE Connectivity		
DIMENSIONS: mm		CHK T.GUO 25MAR2022			
		APVD P.WU 25MAR2022	NAME		
		PRODUCT SPEC	CHERY M1AEV AKI PIGTAIL		
		APPLICATION SPEC	—		
		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-2410747
MATERIAL		FINISH	RESTRICTED TO —		
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 1	REV A1

D

C

B

A

2410747