







D

C

B

A



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10JAN2023	J.S	Z.Z
	A1	ECN-24-258780	03APR2024	J.S	Z.Z

D

C

B

A

NOTE:

- THIS REC HSG ASSEMBLY MATES WITH PLUG ASSEMBLY PN 2445859-X (X=1, 2, 3, 4 FOR VARIOUS CODE).
 - FOR FLANGE VERSION, NEED MATE WITH FIX RING PN 2366517-X.SEE DRAWING 2366517 FOR APPLICABLE WALL THICKNESS.
 - DATE CODE: INDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(21=2021)
MONTH: THIRD DIGIT , EXCLUDING 1 , A=JAN, B=FEB, C=MARCH...(M=DECEMBER)
DAY: FOURTH AND FIFTH DIGITS(14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(11=11AM)
 - IDENTIFICATION FOR CABLE PINOUT.
 - TPA SEATED ON PRE-LOCK POSITION FOR DELIVERY.
 - PULL TPA TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF TPA BEING HIT TO END-LOCK POSITION.
 - REFER TO 114-151006 FOR DT SIZE 12 TERMINAL APPLICATION SPECIFICATION.
REFER TO 114-151001 FOR DT SIZE 16 TERMINAL APPLICATION SPECIFICATION.
REFER TO 114-151003 FOR DT SIZE 20 TERMINAL APPLICATION SPECIFICATION.
APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE:
- | TERMINAL PN | WIRE SIZE (MM2) | INSULATION WIRE (MM2) | PINOUT NUMBER |
|-------------|-----------------|-----------------------|----------------|
| 12# | 4.0-6.0 | Ø3.4-Ø4.3 | 1,2,3,34,35,36 |
| 16# | 0.75-2.5 | Ø1.7-Ø3.0 | 10,17,20,27 |
| 20# | 0.5-1.5 | Ø1.4-Ø2.4 | OTHER PINS |
- FOR FLANGE VERSION THE FACIAL SEAL SEATED IN THE RIGHG POSITION WITH CORRECT DIRECTION.
 - LASER PRODUCT PN. SUCH AS "--1"MEANS 2445860-1, "1--1" MEANS 1-2445860-1.

1	-	-	-	BLUE	PBT-GF30	REAR CAP	4
-	1	-	-	GREEN			
-	-	1	-	GREY			
-	-	-	1	BLACK	VMQ	GROMMET	3
1	1	1	1	RUST RED			
1	-	-	-	BLUE			
-	1	-	-	GREEN			
-	-	1	-	GREY	PBT-GF30	HOUSING CODING D	2
-	-	-	1	BLACK		HOUSING CODING C	
-	-	-	1	BLACK		HOUSING CODING B	
1	1	1	1	YELLOW	PBT-GF30	TPA	1
QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO
A	A	A	A	REVISION OF EACH ASSY PN			
--4	--3	--2	--1	TE ASSEMBLY PN			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

APVD

108-101662

114-32209

WEIGHT

CUSTOMER DRAWING

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

10JAN2023

10JAN2023

10JAN2023

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

NTS 36P REC HSG ASSEMBLY

A2

00779

C=2445860

-

SCALE

SHEET

OF

REV

2:1

1

2

A1

TE Connectivity

C