




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	REVISED PER ECN-25-338302	07AUG2025	TR	NSK



ITEM	NAME	Q'TY	MATERIAL / FINISH
5	CAP	1	LCP,THERMOPLASTIC/UL 94V-0 RATED
4	SPRING CONTACT	4	COPPER ALLOY / Au PLATED
3	FLAT CONTACT	5	COPPER ALLOY / Au PLATED
2	HOUSING	1	PA9T,THERMOPLASTIC/UL 94V-0 RATED
1	SHELL	1	METAL / Ni PLATED

S/N	TE PN	DESCRIPTION	HOUSING COLOR	SHIELD TYPE	CONTACT PLATING (Au)	A	B
1	2439034-1	USB 3.1 A TYPE REC.VT	BLACK	BENDING BOARD LOCK	GF	2.0	0.40
2	2439034-2	USB 3.1 A TYPE REC.VT	BLACK	BENDING BOARD LOCK	15u"	2.0	0.40
3	2439034-3	USB 3.1 A TYPE REC.VT	BLACK	BENDING BOARD LOCK	30u"	2.0	0.40
4	2439034-4	USB 3.1 A TYPE REC.VT	BLACK	BENDING BOARD LOCK	15u"	3.2	0.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.38
1 PLC	± 0.30
2 PLC	± 0.20
3 PLC	± 0.10
4 PLC	± -
ANGLES	± 3
FINISH	-

DWN
GVA
19MAY2023

CHK
DS
18-May-2023

APVD
WH
19-May-2023

PRODUCT SPEC
108-160961

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING


TE Connectivity

NAME
Vertical USB 3.2 A (board lock type)

SIZE A3	CAGE CODE 00779	DRAWING NO C-2439034	RESTRICTED TO -
------------	--------------------	-------------------------	--------------------

SCALE NTS	SHEET 1 of 3	REV B4
--------------	-----------------	-----------

1470-19 (1/15)



△₃ TE LOGO MUST BE CLEAR&LEGIBLE




TABLE A: PIN ASSIGNMENT									
PIN NO	1	2	3	4	5	6	7	8	9
SIGNAL NAME	VBUS	D-	D+	GND	STDA_SSRX-	STDA_SSRX+	GND	STDA_SSTX-	STDA_SSTX+
REMARK	USB 2.0 CONTACT PIN				USB 3.0 CONTACT PIN				

CUSTOMER DRAWING

WEIGHT —

CUSTOMER DRAWING



TE Connectivity




3	NAME	Vertical USB 3.2 A (board lock type)
---	------	--------------------------------------

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A.3 00779 ©-2439034

SCALE	NTS	SHEET	2 OF 3	REV	B4
-------	-----	-------	--------	-----	----

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



5.60KG	2.26KG	150	8	1200	2439034-1
5.60KG	2.26KG	150	8	1200	2439034-2
5.60KG	2.26KG	150	8	1200	2439034-3
5.60KG	2.26KG	150	8	1200	2439034-4
GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	PART NUMBER

NOTES :

1. PACKAGING MATERIAL IN PLASTIC, RUBBER, INK, PIGMENT AND PAINT MUST MEET CONTROLLED SUBSTANCES SPEC PER 230-702.

* CADMIUM AND CADMIUM COMPOUNDS NOT TO EXCEED: 5 PPM.

* LEAD, CADMIUM, CHROM VI AND MERCURY NOT TO EXCEED: 100 PPM (COMBINED).

* CARRIER TAPES, COVER TAPES, REELS AND TAPED COMPONENTS MUST MEET THE REQUIREMENTS DEFINED PER EIA-481-C.

2. MATERIAL :

COVER TAPE : PET, COLOR: TRANSPARENT

CARRIER TAPE : SYNTHETIC MATERIALS, COLOR: BLACK

REEL :PS BLUE

SHIPPING BOX: CORRUGATED FIBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GVA 19MAY2023	 TE Connectivity		
		CHK DS 18-May-2023			
		APVD WH 19-May-2023	NAME Vertical USB 3.2 A (board lock type)		
DIMENSIONS: mm		PRODUCT SPEC 108-160961			
		APPLICATION SPEC			
		—	SIZE A3	CAGE CODE 00779	DRAWING NO C-2439034
MATERIAL —		WEIGHT —	RESTRICTED TO —		
		CUSTOMER DRAWING	SCALE NTS	SHEET 3 of 3	REV B4