






2		1				
LOC	DIST	REVISIONS				
J	-	P	LTR	DESCRIPTION	DATE	APVD
			A	INITIAL	02FEB2024	F.Z




- 1 MATERIAL
- HOUSING: THERMO PLASTICS
- CONTAMINATION Ø1.2 MAX
- CONTACT: COPPER ALLOY
- SPRING: STAINLESS
- 2 PLATING
- CONTACT POINT: UNDER Ni PLATING 0.002mmMIN
- OVER Au PLATING 0.0002mmMIN.
- WIRE CLAMPING POINT: UNDER Ni PLATING 0.002mmMIN,
- OVER Tin PLATING 0.002mmMIN.

1-2474552-1 (11 POSITION KEYING: X)


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER, ZHU 19SEP2023	TE Connectivity					
		CHK RICK, BIAN 19SEP2023						
		APVD RICK, BIAN 19SEP2023						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3		NAME RECEPTACLE ASSEMBLY DYNAMIC D3950				
		0 PLC ±						
		1 PLC ±						
		2 PLC ±						
		3 PLC ±						
		4 PLC ±		SIZE CAGE CODE DRAWING NO RESTRICTED TO				
		ANGLES ±5°						
MATERIAL SEE NOTE		FINISH SEE NOTE		108-161106		A3		
				APPLICATION SPEC 411-78272		C-2474552		
				WEIGHT -		-		
CUSTOMER DRAWING						SCALE 2:1	SHEET 1 OF 2	REV A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-		-	SEE SHEET 1	-	-	-



1-2474552-2 (11 POSITION KEYING: X)

X	11	1-2474552-2
KEYING	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER.ZHU 19SEP2023	TE Connectivity			
DIMENSIONS: mm		CHK RICK.BIAN 19SEP2023				
		APVD RICK.BIAN 19SEP2023	NAME RECEPTACLE ASSEMBLY DYNAMIC D3950			
		PRODUCT SPEC 108-161106				
MATERIAL SEE NOTE		APPLICATION SPEC 411-78272	SIZE A3	CAGE CODE	DRAWING NO C-2474552	RESTRICTED TO -
		WEIGHT -				
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3		CUSTOMER DRAWING				
0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ±5° FINISH SEE NOTE		SCALE 2:1		SHEET 2 OF 2		REV A