




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-231223)	15SEP2023	ED	WH



NOTES:

- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-6GHz
NOMINAL IMPEDANCE : 50 OHMS
INSULATION RESISTANCE : 5000 MOHMS
WORKING VOLTAGE : 335 VRMS MAX
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX
VSWR : 1.3(DC-6GHz)
CONTACT RESISTANCE :
CENTER CONTACT : 6 mOHMS MAX
OUTER CONTACT : 2.5 mOHMS MAX;
- MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
ENGAGEMENT AND DISENGAGEMENT FORCE:
ENGAGEMENT: 14 lbs max;
DISENGAGEMENT: 14 lbs max;
- TEMPERATURE RANGE: -65°-+165°;
- RoHS: COMPLIANT.

	1	NATURAL	PTFE	INSULATOR	7
	1	NATURAL	BERYLLIUM COPPER	RETAINER RING	6
	1	GOLD 30u"/NICKEL/COPPER	BERYLLIUM COPPER	CONTACT PIN	5
	1	NATURAL	PTFE	INSULATOR	4
	1	BRIGHT TIN 200u"/ NICKEL/COPPER	BRASS	HOUSING	3
	1	ELECTROLESS NICKEL 100u"	BRASS	BODY	2
	1	NICKEL 100u"/COPPER	BRASS	SHELL	1
	2466281-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 11SEP2023	 TE Connectivity					
DIMENSIONS: mm		CHK ED 11SEP2023	NAME SMB PLUG,PCB MOUNTING HOLE, RIGHT ANGLE,BULKHEAD,6GHZ —					
	0 PLC ± 0.3 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± — 4 PLC ± — ANGLES ± 5°	APVD WH 11SEP2023						
	PRODUCT SPEC —							
MATERIAL SEE TABLE		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT —	A2	00779	C=2466281	—		
CUSTOMER DRAWING			SCALE	8:1	SHEET	1 of 1	REV	A