


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP PER ECN-23-241561	30NOV2023	ED	WH



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
 FREQUENCY RANGE : DC-18GHz
 NOMINAL IMPEDANCE : 50 OHMS
 INSULATION RESISTANCE : 5000 MOHMS
 WORKING VOLTAGE : 335 VRMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX
 VSWR : 1.3(DC-18GHz)
 CONTACT RESISTANCE :
 CENTER CONTACT : 3 mOHMS MAX
 OUTER CONTACT : 2 mOHMS MAX;
- 4 MECHANICAL CHARACTERISTICS :
 DURABILITY : 500 CYCLES
 TORQUE SETTING : 7-10 IN-LBS;
- 5 TEMPERATURE RANGE: -65°-+165°;
- 6 RoHS: COMPLIANT.

QUANTITY PER ASSY	PARTS LIST
1	NICKEL 100u"/COPPER BRASS COVER 9
1	GOLD 50u"/ NICKEL/COPPER BRASS CONTACT PIN 8
1	PASSIVATION STAINLESS STEEL BODY 7
1	PASSIVATION STAINLESS STEEL SHELL 6
1	PASSIVATION STAINLESS STEEL RETAINER RING 5
1	RED SILICONE GASKET 4
1	GOLD 50u"/ NICKEL/COPPER BRASS CONTACT PIN 3
1	NATURAL PTFE INSULATOR 2
1	PASSIVATION STAINLESS STEEL HOUSING 1
2477465-1	PLATING MATERIAL DESCRIPTION ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 15NOV2023		
DIMENSIONS: mm		CHK ED 15NOV2023		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WH 15NOV2023	NAME	
0 PLC ± 0.3		PRODUCT SPEC		
1 PLC ± 0.2		APPLICATION SPEC		
2 PLC ± 0.1		WEIGHT		
3 PLC ± -		SIZE		
4 PLC ± -		CAGE CODE		
ANGLES ± ± 5'		DRAWING NO		
FINISH -		RESTRICTED TO		
MATERIAL SEE TABLE		A2 00779 C=2477465		
		CUSTOMER DRAWING		
		SCALE 8:1		SHEET 1 OF 1
				REV A

2477465