





| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | A   | NEW DRAWING               | 07JUL2022 | SN  | DM   |
|           | A1  | REVISED PER PCN-22-150096 | 19AUG2022 | MK  | IG   |
|           | A2  | REVISED PER PCN-22-155206 | 12OCT2022 | GB  | DM   |
|           |     |                           |           |     |      |



**SECTION C-C**  
WIRE BARREL


**SECTION B-B**  
INSULATION BARREL

| TE INTERNAL PN | ALIAS PN  | PLATING                                     |
|----------------|-----------|---------------------------------------------|
| 2500036-2      | 936421001 | Selective Ag, Ni overall, Sn/Ni Wire Barrel |


2. SILVER PLATING MAY TARNISH

1. WIRE: 2.50mm<sup>2</sup> FLRY-B & FLRYW-B  
INSULATION RANGE: Ø2.70-3.00

NOTES: UNLESS OTHERWISE SPECIFIED



REELING DIRECTION  
OFF TOP OF REEL

|                                                                                       |  |                                                                                                                  |  |                                                                                                       |                    |
|---------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN 06 JUL 2022<br>N SARATH<br>CHK 07 JUL 2022<br>DAVID MEYER<br>APVD 07 JUL 2022<br>DAVID MEYER                 |  |  TE Connectivity |                    |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±0.13<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |  | NAME<br>BLADE TERMINAL<br>2.50mm <sup>2</sup><br>SRC                                                  |                    |
|  |  | PRODUCT SPEC<br>TEC-108-160021                                                                                   |  | APPLICATION SPEC<br>TEC-114-160021                                                                    |                    |
| MATERIAL<br>COPPER ALLOY                                                              |  | FINISH<br>SEE TABLE                                                                                              |  | WEIGHT<br>0.38g                                                                                       |                    |
| CUSTOMER DRAWING                                                                      |  |                                                                                                                  |  | SIZE<br>A3                                                                                            | CAGE CODE<br>00779 |
| SCALE<br>6:1                                                                          |  |                                                                                                                  |  | DRAWING NO<br>C-2500036                                                                               | RESTRICTED TO<br>- |
| SHEET<br>1 OF 1                                                                       |  |                                                                                                                  |  | REV<br>A2                                                                                             |                    |