







1) NUMERI DI IDENTIFICAZIONE CAVITA' (CIRCUIT IDENTIFICATION)

2) MARCHIO DI FABBRICA (TRADEMARK)

3) OBSOLETO (OBSOLETE)

5) INCLUDE LA POLARIZZAZIONE DOVE E' ESISTENTE (INCLUDING POLARIZATION KEY, WHEN EXISTING)

7) STATO DI FORNITURA: CONFEZIONAMENTO "IN VASSO (PACKAGING: "ON TRAY PLUS CARTON BOX")



PASSO 11.4-12.4
(PITCH)

2	BLOCCHETTO (HOUSING)			NATURALE (NATURAL)		POLIAMMIDE 6.6 20% C.V. AKULON (P.A. 6.6 20% G.F. AKULON R622)			4		
	1	CONTATTO (CONTACT)			STAGNATO (TIN-PLATED)		OTTONE (BRASS)				
ITEM		DENOMINAZIONE			FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)				
					CUSTOMER DRAWING FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO			
					THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION 19			
					© COPYRIGHT 1986 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING						
E1	REVISED PER ECR-23-193138			AK DC	04DEC 2023	TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO			DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)	SCALA (SCALE)
E	NEW PACKAGING SPEC. ON TRAY REVISED - ET00-0099-00			GS CT	19.04 00				-	0.5 - 1.5mm2	-
D2	REVISED FOR ET00-0264-97			A.F.	.	(TOLERANCES: UNLESS OTHERWISE SPECIFIED)					
D1	OBSOLETE TO EC 0498-96			G.E.	04.11 97	± 0.3			 AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)		
D	REVISED TO EC 0339-96 RELEASED FOR PRODUCTION			G.E.	24.09 96	ANGOLI (ANGLES) ± 2°					
4	AGGIUNTO CODICE			G.S.	11.7 89	DIS. G. ENDRIZZI (DR.) 23.07.96			DESCRIZIONE (DESCRIPTION) MONO SHAPE MK I, SATELLITE CONNECTOR		
3	AGGIUNTO TOLLERANZE			G.S.	1.3 89						
2	ADDED TRADEMARK			G.S.	7/12 88	CONT. G. VIGNOLI (CHK) 23.07.96			LOC. SIZE NUMERO (DWG NO.) I A3 C-282099		
1	REVISED			G.S.	9.11 88	APP. - (APP.)					
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)			DIS. (DR)	DATA (DATE)	REV. FOGLIO (SHEET) E1 DI (OF) 2					

NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto) ①	P/N ASS'Y IN VASSOIO	P/N ASS'Y IN BOBINA	REV.	POSIZIONE POLARIZ. (LATO POSTERIORE)	POSIZIONE AGGANCIO (LATO ANTERIORE)	POSIZIONE POLARIZZAZIONE PARTICOLARE (LATO ANTERIORE)	6 L +0.2 -0.3 (mm)	RAW MATERIAL
NO. OF POS.	CONFIGURATION (View from top side) ①	P/N ASS'Y ON TRAY	P/N ASS'Y ON REEL	PART REV.	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL CODIFICATION POSITION (FRONT SIDE)	L +0.2 -0.3 (mm)	RAW MATERIAL
3		3 282099-1	-	-	ID	1-2		14.9	4
		1-282099-1 3	-	E					
3		-	0-284741-1 3	E	ID	1-2		14.9	5

LEGENDA

(DESCRIPTION)

IDC CONNETTORE MASCHIO 5mm passo
(IDC TAB CONNECTOR 5mm pitch)
① (Esempio di configurazione)
(Example of configuration)

FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DRAWING FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO			
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES: UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
± 0.3		-		-	
ANGOLI (ANGLES)		± 2°		-	
DIS. G. ENDRIZZI (DR.) 23.07.96		tyco Electronics AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)			
CONT. G. VIGNOLI (CHK) 23.07.96					
DESCRIZIONE (DESCRIPTION)		MONO SHAPE MK I, SATELLITE CONNECTOR			
LOC. SIZE		NUMERO (DWG NO)		REV. FOGLIO (SHEET)	
1 A3		C-282099		E1 2 DI (OF) 2	
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)	DIS. (DR)	DATA (DATE)	APP. (APP.)	

DISTRIBUZIONE
(PRINT DIST.)